


Straight Flow Basket Strainer



Model 73 Straight flow



- Iron or bronze
- Sizes 10" to 18"
- Flanged

Features

- Quick open cover
- Straight through flow design
- Low pressure loss
- Convoluted basket design
- Hand removable basket
- Threaded drain
- Buna-N® O-ring seal
- Perforated or mesh 316 stainless steel basket
- Low profile
- American Bureau of Shipping (ABS) Type Approved for ship designers, builders and owners



Options

- Basket perforations from 1/32" to 1/2"
- Basket mesh of 20, 40 or 60
- MONEL® baskets
- Vent valves
- Drain valves
- Gauge/vent taps - 1/4" NPT
- Pressure differential gauge and switches

MONEL® is a registered trademark of Special Metals Corporation group of Companies.

The Best simplex strainer for high flow applications in large pipelines

The Eaton Model 73 simplex basket strainer with its straight flow design greatly reduces pressure loss and results in a compact strainer that can fit in tight spaces.

Special basket strainer

Large size pipelines with high flow rates require a specific type of basket strainer. The convoluted (pleated) perforated or mesh screens in the basket increases the amount of straining area available while reducing the basket size and weight. This makes it easy to remove the basket from the strainer housing. No lifting tackle required. The quick opening cover provides fast

and easy access to the basket for quick service. This can save considerable time and money in labor.



When selecting a pipeline strainer for a large size piping system with high flow rates, be sure to consider all the factors, not just initial pressure loss. The amount of straining area in the basket is critical to reducing the amount of time between cleanings or changeouts.



EATON

Powering Business Worldwide

Model 73 Straight Flow Strainer



Selection chart

Size	Material	End connection	Seals	Pressure rating*
10" to 12"	Iron	Flanged 125#	Buna-N	200 psi (13.8 bar)
10" to 12"	Bronze	Flanged 150#	Buna-N	200 psi (13.8 bar)
14" to 18"	Iron	Flanged 125#	Buna-N	150 psi (10.3 bar)
14" to 18"	Bronze	Flanged 150#	Buna-N	150 psi (10.3 bar)

* @ 100 °F (38 °C)

Cv factors*

Size	Value
10"	2300
12"	3200
14"	5000
16"	6000
18"	7000

* For water with clean, perforated basket

Dimensions (in/mm) Model 73 straight flow

Pipe size	A		B		C		D		F		G		H		Net Wt (lb / kg)			
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	Iron	Bronze		
10	23.00	584	11.00	279	12.19	310	29.00	737	47.00	1194	19.00	483	15/16	24	420	191	500	227
12	27.00	686	13.00	330	16.75	425	38.00	965	67.00	1702	23.00	584	1	25	550	250	825	374
14	31.00	787	15.50	394	18.75	476	45.00	1143	77.00	1956	27.00	686	1	25	850	386	1150	522
16	31.00	787	15.50	394	18.75	476	45.00	1143	77.00	1956	27.00	686	1	25	975	443	1400	635
18	31.00	787	15.50	394	18.75	476	45.00	1143	77.00	1956	27.00	686	1	25	1000	454	—	—

Dimensions and weights are for reference only. Contact Eaton for certified drawings.

North America
44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

Europe/Africa/Middle East
Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0

Internormen Product Line
Friedensstraße 41
68804 Altlufsheim, Germany
Tel: +49 6205 2094-0

Begerow Product Line
An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

China
No. 3, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 5200-0099

Singapore
4 Loyang Lane #04-01/02
Singapore 508914
Tel: +65 6825-1668

Brazil
Av. Julia Gaioli, 474 – Bonsucesso
07251-500 – Guarulhos, Brazil
Tel: +55 11 2465-8822

For more information, please
email us at filtration@eaton.com
or visit www.eaton.com/filtration

© 2014 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US
EF-SSEA-6
6-2014