

## Integrity Testing Device BECO® MAX<sub>2</sub>

BECO MAX<sub>2</sub> provides integrity testing for unparalleled accuracy and decision-making. An easy-to-use keypad and backlit 4-line display automatically tests the integrity of membrane filter cartridges.

The water-resistant, stainless steel housing protects the device from splashes of water and delivers long-lasting battery life. The spiral coiled tubes allow the user to easily connect the device in hard to reach places.

Save and print up to 10 programs and 40 performance data.

Input values, single input:

- Testing pressure
- Stabilizing time
- Testing time
- Max. admissible pressure drop
- Medium- and housing data

The testing device is capable of measuring membrane cartridges in small-volume housings (< 0.9 gal (< 3.5 l)) as well as large-volume housings (0.9 – 40 gal/ 3.5 – 150 l).

### Technical Data

- Housing material: stainless steel AISI 304
- Splash water proof IP55
- Backlit 4-line display
- Languages available: German, English, French, Italian, Spanish, Danish or Swedish (on request)
- Measuring range 9.5 – 40 psi (650 – 2,800 mbar)
- Battery: NimH 7.2 V, 4.5 Ah
- Ambient temperature 41 – 104 °F (5 – 40 °C)
- Rel. humidity 0 – 80%
- Lock clutch and plug nipple Rectus DN 7.2



### Scope of Supply

- Integrity testing device for fully automatic measurement of diaphragm filter cartridges
- Padded plastic transport box
- Power supply unit, battery recharge unit
- Input keypad
- Data cable
- Dot matrix printer with power supply unit, printer cable, spare paper rolls (2.24" (57 mm)) and spare ink ribbon
- Documentation (operating manual, calibration certificate)

### Delivery Information

Article No.: P5001000

**North America**  
44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

**China**  
No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

**Europe/Africa/Middle East**  
Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0  
  
Friedensstraße 41  
68804 Altlußheim, Germany  
Tel: +49 6205 2094-0

**Singapore**  
100G Pasir Panjang Road #07-08  
Singapore 118523  
Tel: +65 6825-1668

An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

**Brazil**  
Av. Ermano Marchetti, 1435 -  
Água Branca, São Paulo - SP,  
05038-001, Brazil  
Tel: +55 11 3616-8461

**For more information, please  
email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)**

EN  
1 A 7.4.2.1  
07-2019

© 2019 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.