


## Enclosed Plate and Frame Filter BECO INTEGRA® PLATE 600 DP

### Stainless Steel Chassis, Plastic Filter Plates, and Cake Frames

BECO INTEGRA PLATE 600 DP enclosed plate and frame filter is the depth filtration system for critical filtration tasks in the pharmaceutical and biotech, chemical, cosmetics, and food industries.

BECO INTEGRA PLATE 600 DP is a multi-sheet-filter in enclosed design. The product channels are sealed with depth filter sheets only. The sealing of the filter package is realized by means of O-rings at the outer edge of the filter package.



#### Special Features

- **CIP** of filter package without depth filter sheets.
- **Complete drainage** of filter due to unique filter plate design.
- **Safe operation:** No drip loss due to sealing of filter package by means of O-rings and automatic hydraulic pressure regulation.
- **Easy handling** and **good cleanability** thanks to ergonomic design of chassis, and open support grid of filter plates; cake discharge downwards into tray underneath of filter package.
- **High flexibility:** The filter can be used as a sheet filter or as a pre-coat filter. For pre-coating/removing of high particle load, cake frames in different widths are available.
- BECO INTEGRA PLATE 600 DP filter is designed and manufactured according to the **cGMP guidelines** and the **FDA regulations**.

Customization or additional components allow for system expansion or complete systems according to customer specifications.

#### Technical Data

<b>Operating pressure/temp.:</b>	max. 87 psi (600 kPa/6 bar) at 104 °F (40 °C) max. 43 psi (300 kPa/3 bar) at 140 °F (60 °C)
<b>Differential pressure/temp.:</b>	max. 43 psi (300 kPa/3 bar) at 104 °F (40 °C)
<b>Filter area per sheet:</b>	3.1 ft² (0.29 m²)

#### Materials

<b>Product contacting parts:</b>	Stainless steel AISI 316L, Polypropylene
<b>Other parts:</b>	Stainless steel AISI 304
<b>Gaskets/O-rings:</b>	Silicone, EPDM, Viton, FEP coated (FDA listed)



Powering Business Worldwide

Type	Filter area		Cake volume*		Chassis size	Filter plates/ cake frames	Depth filter sheets 22.6 x 26.0 in (573 x 661 mm)	Weight	
	ft <sup>2</sup>	(m <sup>2</sup> )	gal	(l)				qty	qty
<b>600 SF/ASF</b> with 0.79" (20 mm) cake frames	81.16	(7.54)	14.79	(56)	1	12/13	26	2,934	(1,331)
	143.59	(13.34)	24.42	(100)	2	22/23	46	3,294	(1,494)
	206.02	(19.14)	37.78	(143)	3	32/33	66	3,600	(1,633)
	312.15	(29.00)	57.33	(217)	4	49/50	100	4,165	(1,889)
<b>600 ASF</b> with 1.57" (40 mm) cake frames	56.19	(5.22)	23.78	(90)	1	8/ 9	18	2,899	(1,315)
	106.13	(9.86)	44.91	(170)	2	16/17	34	3,261	(1,479)
	149.83	(13.92)	63.40	(240)	3	23/24	48	3,541	(1,606)
	224.75	(20.88)	95.10	(360)	4	35/36	72	4,065	(1,844)
<b>600 ASF</b> with 2.36" (60 mm) cake frames	43.70	(4.06)	29.59	(112)	1	6/ 7	14	2,884	(1,308)
	81.16	(7.54)	54.95	(208)	2	12/13	26	3,225	(1,463)
	118.62	(11.02)	80.31	(304)	3	18/19	38	3,512	(1,593)
	175.02	(16.26)	118.35	(448)	4	27/28	56	4,006	(1,817)

\* usable cake volume

### Filter Plates/Cake Frames

	Width	Cake volume*		Weight	
	in (mm)	gal	(l)	lb	(kg)
Initial / end plate	0.98 (25)			19.8	(9.0)
Filter plate	0.98 (25)			18.7	(8.5)
Feeding plate	0.98 (25)			18.7	(8.5)
Cake frame	0.79 (20)	1.15	(4.35)	6.6	(3.0)
Cake frame	1.57 (40)	2.64	(10.00)	13.2	(6.0)
Cake frame	2.36 (60)	4.23	(16.00)	19.8	(9.0)

\* usable cake volume

### Connections


Filter inlet:	DN 25, DIN 11851/ISO 2 ½"
Filter outlet:	DN 25, DIN 11851/ISO 2 ½"

### Other Types

Filter elements also available in PVDF

Flange connections DIN 2633/ISO or tri-clamp on request

Full product processing also available in PP or PVDF





**North America**  
44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

**Europe/Africa/Middle East**  
Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0  
  
Friedensstraße 41  
68804 Altlußheim, Germany  
Tel: +49 6205 2094-0

An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

**China**  
No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

**Singapore**  
4 Loyang Lane #04-01/02  
Singapore 508914  
Tel: +65 6825-1668

**Brazil**  
Rua Clark, 2061 - Macuco  
13279-400 - Valinhos, Brazil  
Tel: +55 11 3616-8400

**For more information, please  
email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)**

EN  
1 A 2.6.11.4  
10-2016

© 2016 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.