


# Application Data 32 - 880

## Characteristic Curves for Types DSII and DSLII Circuit Breakers

Cutler-Hammer



**DSII Low Voltage AC Power Circuit Breaker**  
 Equipped With 200-1200 Amp Digitrip OPTIM Trip Units  
 Response: LONG DELAY  $I^2t$ , SHORT DELAY  $I^2t$

Available Rating Plugs				
Maximum Ampere Rating	Ampere Rating ( $I_n$ )	Rating Plug Catalog Number	Long Delay Pickup Range 0.5 to $1 \times I_n$ Amperes	Short Delay Pickup Range 1.5 to $10 \times I_n$ Amperes
200	200	RP6D02A020	100- 200	150- 2000
	100	RP6D02A010	50- 100	75- 1000
300	300	RP6D03A030	150- 300	225- 3000
	250	RP6D03A025	125- 250	188- 2500
	200	RP6D03A020	100- 200	150- 2000
400	400	RP6D04A040	200- 400	300- 4000
	300	RP6D04A030	150- 300	225- 3000
	250	RP6D04A025	125- 250	188- 2500
	200	RP6D04A020	100- 200	150- 2000
600	600	RP6D06A060	300- 600	450- 6000
	400	RP6D06A040	200- 400	300- 4000
	300	RP6D06A030	150- 300	225- 3000
800	800	RP6D08A080	400- 800	600- 8000
	600	RP6D08A060	300- 600	450- 6000
	400	RP6D08A040	200- 400	300- 4000
1200	1200	RP6D12A120	600-1200	900-12000
	1000	RP6D12A100	500-1000	750-10000
	800	RP6D12A080	400- 800	600- 8000
	600	RP6D12A060	300- 600	450- 6000

Interrupting Ratings @ 50/60 Hz RMS Sym. Amperes (kA)							
Breaker Type	Maximum Frame Size Amperes	UL/CSA					
		Instantaneous Trip			Short Delay Trip		
		240	480	600	240	480	600
DSII-308	800	42	30	30	30	30	30
DSII-508	800	65	50	42	50	50	42
DSII-608	800	65	65	50	65	65	50
DSII-516	1600	65	50	42	50	50	42
DSII-616	1600	65	65	50	65	65	50
DSII-620	2000	65	65	50	65	65	50
DSLII-308	800	200	200	200			
DSLII-516	1600	200	200	200			

**Notes:**

- There is a memory effect that can act to shorten the long delay. The memory effect comes into play if a current above the long delay pickup value exists for a time and then is cleared by the tripping of a downstream device or the circuit breaker itself. A subsequent overload will cause the circuit breaker to trip in shorter time than normal. The amount of time reduction is inverse to the amount of time that has elapsed since the previous overload. Approximately five minutes is required between overloads to completely reset the memory.
- The end of the curve is determined by the interrupting rating of the circuit breaker. See above tabulation.
- For ground fault time / current curves see SC-6283-96.
- The Long Delay Pick-up Point (indicated by a flashing LED on the product) nominally occurs at 105% of the  $I_r$  current, with a  $\pm 5\%$  tolerance. The short delay settings have conventional 100%,  $\pm 5\%$  as the pick-up points.
- With Zone Interlocking on Short Delay utilized and no restraining signal, the minimum time band applies regardless of the setting.
- This curve is shown as a multiple of the Long Delay Pick-up Setting ( $I_r$ ). This  $I_r$  setting is programmed in primary value amperes via a Breaker Interface Module, or OPTIMizer, or a Remote PC (IMPACC System).
- For additional curve tolerances contact Cutler-Hammer.
- Total clearing times shown include the response times of the trip unit, the breaker opening, and the extinction of the arcing current.