Magnum switchgear with Series NRX breaker integration



When building space is at a premium, or when system upgrades require additional building loads, equipment dimensions can present a challenge. To meet this challenge, Eaton offers Magnum™ low-voltage switchgear with Series NRX™ breaker integration.

Features

- Up to eight 800 ampere UL® 1066 circuit breakers in a 24-inch-wide UL 1558 switchgear assembly
- Two Series NRX breakers can be mounted side-by-side in the same space typically used for a Magnum DS breaker
- Dedicated breaker secondary terminal blocks are easily accessible while keeping the breaker doors closed
- Breakers have a drawout design that allows for through-the-door racking
- One-piece molded support for load-side bus in cable compartment
- 100,000 ampere bus bracing as standard, with option for 150,000
- Electronic trip unit innovation including Arcflash Reduction Maintenance System™


Benefits

- Space savings of up to 45 percent
- Arc-flash reduction capabilities
- Through-the-door design, allowing full breaker operation with door closed
- Increased flexibility in layout due to ability to mix Magnum DS and Series NRX breakers in a single structure
- Rogowski sensors are rated between 200 and 1200 amperes, meaning that sensors do not need to be replaced for breaker upgrades


Standards

- UL 1066, UL 489, UL 1558, UL 891
- ANSI C37.51, C37.50, C37.20.1, ANSI C37.17
- ANSI C37.15 listed for low-voltage equipment






Main with feeders One MDS and four Series NRX feeders in 24-inch structure



Tie with feeders One MDS and six Series NRX feeders in 24-inch structure




Feeders only Eight feeders in 24-inch structure



Feeders only Two MDS feeders and four Series NRX feeders in 24-inch structure

Standard Magnum feeder sections Series NRX feeder section Two 22-inch Two 18-inch One 24-inch structure structures with structures with with eight Series NRX four MDS breakers four MDN breakers breakers **Tight** Space? is the Solution **Smaller** Larger **Footprint Reduced By 45%**



MDS



Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

© 2018 Eaton All Rights Reserved Printed in USA Publication No. SA01900004E / Z20416 February 2018

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.











