

TIME-CURRENT CHARACTERISTIC CURVES

MINIMUM MELT
23.0kV ELSP BACK-UP TYPE OIL IMMERSIBLE CURRENT LIMITING FUSE

Tests made at LOW Volts ac at HIGH pf at 25°C with no initial load
Standards used as basis for data: ANSI C37.47-1981 (R1992)


MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE PLUS

THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.

Reference Data
R240-91-67
Page 1 of 2

COOPER Power Systems
COMPONENTS AND PROTECTIVE EQUIPMENT

DRAWN BY: DKS [CHKD] DATE: 07-16-97
REPLACES: 04/95 [REV 03] REQ NO. 17661
DWG NO. 42 04833 B 00



TIME-CURRENT CHARACTERISTIC CURVES

MAXIMUM CLEAR
23.0kV ELSP BACK-UP TYPE OIL IMMERSIBLE CURRENT LIMITING FUSE

Tests made at RATED Volts ac at LOW pf at 25°C with no initial load
Standards used as basis for data: ANSI C37.47-1981 (R1992)

MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE MINUS

THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.

Reference Data
R240-91-67
Page 2 of 2

COOPER Power Systems
COMPONENTS AND PROTECTIVE EQUIPMENT

DRAWN BY: DKS [CHKD] DATE: 07-16-97
REPLACES: 04/95 [REV 03] REQ NO. 17661
DWG NO. 42 04833 B 00