


| | | | |
|--|--|---|--|
| | | TIME-CURRENT CHARACTERISTIC CURVES | |
| | | MINIMUM MELT 23.0kV MINI-ELSP BACKUP TYPE OIL IMMERSIBLE CURRENT LIMITING FUSE | |
| DRAWN BY: EKS DATE: 07-17-97 REPLACES: 08/91 REV: 04 REG. NO. 17661 DWG. NO.: 42 38615 B 00 | [CHKD] Tests made at LOW Volts ac at HIGH pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1991 (R1992) MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE PLUS | THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT. | |

Reference Data
 R240-91-66
 Page 1 of 2



| | | | |
|--|--|--|--|
| | | TIME-CURRENT CHARACTERISTIC CURVES | |
| | | MAXIMUM CLEAR 23.0kV MINI-ELSP BACKUP TYPE OIL IMMERSIBLE CURRENT LIMITING FUSE | |
| DRAWN BY: EKS DATE: 07-17-97 REPLACES: 08/91 REV: 04 REG. NO. 17661 DWG. NO.: 42 38615 B 00 | [CHKD] Tests made at RATED Volts ac at LOW pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1991 (R1992) MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE MINUS | THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT. | |

Reference Data
 R240-91-66
 Page 2 of 2