

# Champ Pro PFMA LED floodlights

3,000 to 7,000 lumens

UL Listed  
CSA Certified  
Marine & Wet Locations  
Type 4X; IP66

5L

## Applications:

- For general area illumination of locations with mounting heights from 9-15 feet
- Locations requiring continuous and consistent light levels in extreme ambient temperatures
- Extremely corrosive, wet, dusty, hot and/or cold conditions
- IP66, Type 4X, marine, wet locations and hose down environments
- Manufacturing plants; heavy industrial, chemical, food and beverage facilities; mining; platforms; loading docks; tunnels; outdoor wall and pole mounted areas

## Certifications and compliances:

### NEC/CEC:

- Marine and wet locations, Type 4X, IP66
- ABS

### UL standards:

- UL1598
- UL1598A
- UL50E

### CSA standard:

- C22.2 No. 250

### FCC part 15/ICES-005 ver. 5:

- CAN ICES-005 (A)/NMB-005 (A)

## Standard materials:

- Lamp housing and adapter – die cast aluminum with Corro-free epoxy powder coat
- Lens – heat- and impact-resistant glass (standard); diffused glass, clear polycarbonate, diffused polycarbonate (optional)
- Gaskets – silicone
- External hardware – stainless steel
- Factory sealed, no external seals required

## Electrical ratings:

Model	Weight lbs. (kg.)	Nominal lumens	Efficacy	Wattage	Voltage	Amps	Power factor	THD	Surge protection
PFMA-3-UNV1	14.70 (6.67)	3,400	111 lm/W	30.7	120-277 VAC, 50/60 Hz; 125-250 VDC	0.26	0.90	≤ 20%	6kV
PFMA-5-UNV1	14.70 (6.67)	5,200	116 lm/W	44.9	120-277 VAC, 50/60 Hz; 125-250 VDC	0.37	0.90	≤ 20%	6kV
PFMA-7-UNV1	14.70 (6.67)	6,800	115 lm/W	59.1	120-277 VAC, 50/60 Hz; 125-250 VDC	0.50	0.90	≤ 20%	6kV
PFMA-3-UNV3	14.70 (6.67)	3,400	111 lm/W	30.3	347-480 VAC, 50/60 Hz	0.09	0.90	≤ 20%	6kV
PFMA-5-UNV3	14.70 (6.67)	5,200	116 lm/W	43.7	347-480 VAC, 50/60 Hz	0.13	0.90	≤ 20%	6kV
PFMA-7-UNV3	14.70 (6.67)	6,800	115 lm/W	56.2	347-480 VAC, 50/60 Hz	0.16	0.90	≤ 20%	6kV



## LED system:

- High intensity discrete power emitters
- Cool white (5000K, 70 CRI) standard; warm white (3000K, 80 CRI) or neutral white (4000K, 70 CRI) (optional)
- NEMA 6x6 optical pattern
- Dimmable driver 0-10V

## Photometrics:

- Refer to [www.eaton.com](http://www.eaton.com) (under the Resources tab of each product family) for specific photometric IES files

# Champ Pro PFMA LED floodlights


3,000 to 7,000 lumens

UL Listed  
CSA Certified  
Marine & Wet Locations  
Type 4X; IP66

5L

## Design features:

Our Champ LED floodlight is a field-proven design that helps ensure safety, reliability and performance in harsh and heavy industrial areas. The new form factor is engineered to deliver more operational value and better total cost of ownership.




## INSTALLATION EASE

### A Easy access

- Removable covers for LED engine and driver compartments enable faster installation, access to wiring and field maintenance


### B Lever lock connectors and terminal blocks

- Plug and play wiring simplifies and speeds installations



### C Versatile mounting options

- Standard yoke mount and optional wall and hub mounts help ensure that the fixtures are installed in the correct location to properly light your facility



Yoke mount  
(standard)

Hub mount

Wall mount

# Champ Pro PFMA LED floodlights

3,000 to 7,000 lumens


UL Listed  
CSA Certified  
Marine & Wet Locations  
Type 4X; IP66

5L

## LONG-LIFE RELIABILITY

### D Thermal management

- Heat fins help ensure proper air flow and facilitate dust shedding for effective heat dissipation and thermal management of LED engine



### E Performance in extreme environments


- Operating ambient: -40°C to 65°C
- Type 4X, IP66
- 6kV surge protection
- Corrosion-resistant aluminum housing with Corro-free epoxy powder coating
- Vibration tested in accordance with Section 33 of UL844
- Impact tested in accordance with Section 68 of UL844



## LIGHT PERFORMANCE & QUALITY

### F Custom optics & colors

- Directs light where you need it, helping eliminate gaps and dark spots
- Can potentially reduce the number of light fixtures required in your application
- 3000K (warm), 4000K (neutral) and 5000K (cool) color options available



### NEMA 6x6

Large circular distribution pattern for indoor and outdoor area lighting



### 5000K – cool

Crisp, bright white with a blue hue



### 3000K – warm

Warm white with a yellow hue

### G Multiple lens & epoxy powder coat options

- Clear glass lens standard; diffused glass and clear or diffused polycarbonate lenses (optional)
- Corro-free epoxy powder coat available in gray (standard) or white and bronze (optional)



White



Gray



Bronze

# Champ Pro PFMA LED floodlights

3,000 to 7,000 lumens

UL Listed  
 CSA Certified  
 Marine & Wet Locations  
 Type 4X; IP66

5L

## Ordering information:

Part number example

PFMA-3-W-T-66-DP-GV-UNV1-WH-PC2-M2

# PFMA - 3 - W - T - 66 - DP - GV - UNV1 - WH - PC2 - M2

### Light source / intensity

<b>3L</b>	3,400 nominal lumens
<b>5L</b>	5,200 nominal lumens
<b>7L</b>	6,800 nominal lumens

### Color temperature

<b>BLANK</b>	5000K, 70 CRI (cool white)
<b>N<sup>A</sup></b>	4000K, 70 CRI (neutral white)
<b>W</b>	3000K, 80 CRI (warm white)

### Mounting

<b>BLANK</b>	Yoke mount
<b>H</b>	Hub mount
<b>T</b>	Wall mount

### Optics

<b>66</b>	6x6 beam spread
-----------	-----------------

### Lens material

<b>BLANK</b>	Clear glass
<b>DG</b>	Diffused glass
<b>PC</b>	Polycarbonate
<b>DP</b>	Diffused polycarbonate

### Guard and visor

<b>BLANK</b>	None
<b>G</b>	Bolt-on wire guard
<b>V</b>	Visor
<b>GV</b>	Bolt-on wire guard & visor

### Voltage

<b>UNV1</b>	120-277 VAC, 50/60 Hz; 125-250 VDC
<b>UNV3</b>	347-480 VAC, 50/60 Hz

### Paint

<b>BLANK</b>	Gray
<b>WH</b>	White
<b>BZ</b>	Bronze


### Sensor

<b>BLANK</b>	No sensor included
<b>PC1<sup>B</sup></b>	120V photocell
<b>PC2<sup>B</sup></b>	208-277V photocell

## Accessories (ordered separately):

### Description

Description	Cat. #
• Visor.....	<b>DSV4</b>
• Bolt-on wire guard.....	<b>P64</b>
• Safety cable.....	<b>SC831</b>
• Floodlight slipfitter.....	<b>SFA6</b>
• Slipfitter wall mount adapter.....	<b>SWB6</b>



### Replacement driver kits (ordered separately)

<b>FMVA-3-5-7-UNV1-M2-DRIVER KIT</b>	UNV1 M2 replacement driver kit for FVMA-3, -5 and -7
<b>FMVA-3-5-7-UNV3-M2-DRIVER KIT</b>	UNV3 M2 replacement driver kit for FVMA-3, -5 and -7
<b>FMVA-3-5-7-UNV1-PC-M2-DRIVER KIT</b>	For use in models with photocell; UNV1 M2 replacement driver kit for FVMA-3, -5 and -7

<sup>A</sup>Consult customer service for lead time.

<sup>B</sup>For use with UNV1 models only.


# Champ Pro PFMA LED floodlights

3,000 to 7,000 lumens

UL Listed  
 CSA Certified  
 Marine & Wet Locations  
 Type 4X; IP66

5L

## Dimensions – standard yoke mount:



5L

Mounting method	Angle range	Mounting surface
Yoke (standard)	+45° to -90°	Wall, ceiling, horizontal surface/ground




# Champ Pro PFMA LED floodlights

3,000 to 7,000 lumens

UL Listed  
 CSA Certified  
 Marine & Wet Locations  
 Type 4X; IP66

5L

## Dimensions – hub mount (optional):



Mounting method	Angle range	Mounting surface
Hub	+45° to -90°	Wall, ceiling, horizontal surface/ground

5L


# Champ Pro PFMA LED floodlights

3,000 to 7,000 lumens

UL Listed  
 CSA Certified  
 Marine & Wet Locations  
 Type 4X; IP66

5L

## Dimensions – wall mount (optional):



Mounting method	Angle range	Mounting surface
Wall	Fixed	Wall

5L