


 COMPONENTS AND PROTECTIVE EQUIPMENT		TIME-CURRENT CHARACTERISTIC CURVES	
		MINIMUM MELT TIME-CURRENT CHARACTERISTICS CURVES B, 3, 15, 5, 23, 0KV ELSG FULL RANGE UNDER-OIL CURRENT LIMIT FUSE	
Tests made at LOW Volts at all HIGH pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1981 (R1992)		MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE PLUS	
THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.		THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.	
* THE 135 AMP RATING IS AVAILABLE ONLY AT 23.0KV.		Reference Data R240-91-88 Page 1 of 2	



 COMPONENTS AND PROTECTIVE EQUIPMENT		TIME-CURRENT CHARACTERISTIC CURVES	
		MAXIMUM CLEAR TIME-CURRENT CHARACTERISTICS CURVES B, 3, 15, 5, 23, 0KV ELSG FULL RANGE UNDER-OIL CURRENT LIMIT FUSE	
Tests made at RATED Volts at all LOW pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1981 (R1992)		MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE MINUS	
THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.		THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.	
* THE 135 AMP RATING IS AVAILABLE ONLY AT 23KV.		Reference Data R240-91-88 Page 2 of 2	