

## Incandescent Accessories

### Applications:

The incandescent VS Portable Hand Lamps are used:

- In wet or corrosive locations to exclude moisture, dirt, corrosive chemicals, etc.
- Where an incandescent lamp of up to 100 watts is required in a portable hand lamp

### Features:

- Enclosed and gasketed
- Flexible cord or cable is attached through a watertight gland in the handle
- Is of rugged construction
- Clamp type guard available
- Provision is made in the lamp receptacle for a third conductor to ground all non-current carrying metal parts

### Certifications and Compliances:

- Weather resistant
- UL Standard: 298

(Note: CEC/CSA Certified VS Hand Lamps - Eaton's Crouse-Hinds Canada fixtures only).

### Standard Materials:

- Handle – molded rubber
- Globe – clear, plain glass
- Guard – cast aluminum or steel wire

### Standard Finishes:

- Handle – natural
- Guard – zinc plated

### Size Ranges:

- Up to 100 watt, A-23 lamp
- 0.250 to 0.625 cord O.D.



(No Cable Included)

Globe Length	Max. Lamp Size	Cord Dia.	Rubber Cat. #
6 <sup>7</sup> / <sub>8</sub> "	100W A-23*	0.125 to 0.625	<b>VS30</b>

Note: Furnished with clear globe, wire guard and 4 rubber bushings.

### Glass Globes



**Description**  
Clear Glass,  
(Heat Resisting)

### Polycarbonate Globes



Description	Maximum Lamp Size	Cat. #
Clear Glass, (Heat Resisting)	100W, A-23 – 6 <sup>7</sup> / <sub>8</sub> "**	<b>V63</b>
Clear, Polycarbonate, Plain	75W, A-21**	<b>V470</b>

### Guards




Description	Size	Cat. #
Steel Wire	6 <sup>7</sup> / <sub>8</sub> " Globe	<b>VS97</b>

### Lamp Receptacle (medium base)



Description	Size	Cat. #
Composition keyless	660W, 600V	<b>GS156</b>

### Cord Gland Bushings



Description	Size	Cat. #
Rubber	0.125 to 0.250 Cord	<b>BUSH92</b>
	0.250 to 0.375 Cord	<b>BUSH93</b>
	0.375 to 0.500 Cord	<b>BUSH94</b>
	0.500 to 0.625 Cord	<b>BUSH05</b>

\*Will take lamps with maximum dimensions of 6<sup>1</sup>/<sub>2</sub>" long and 2<sup>1</sup>/<sub>2</sub>" diameter.

