

600 A 35 kV class standoff bushings



General

Eaton meets the full requirements of IEEE Std 386™-2006 standard—Separable Insulated Connector Systems, with its Cooper Power™ series 600 A, 35 kV insulated standoff bushing providing a single deadbreak interface made of high quality insulating epoxy material. It is used in pad-mounted cabinets, underground vaults, and other apparatus to isolate and sectionalize an energized cable.

Temporary or permanent parking of energized 600 A 35 kV deadbreak connectors that conform to IEEE Std 386™-2006 standard is simplified with the use of insulated standoff bushings.

The insulated standoff bushing is designed to be installed in the parking stand mounted on a transformer or other apparatus. A drain wire lug is provided on the standoff bracket for attachment of a drain wire to ensure deadfront construction. The bushing provides a fully-shielded, submersible connection for deadbreak operation.

Eaton's Cooper Power series 600 A, 35 kV grounded standoff bushing is designed to be installed in the parking stand bracket mounted on the transformer or other apparatus.

A 2/0 AWG copper, 5-foot jacketed cable is connected to the all-aluminum bushing for attachment to system ground. The bushing provides a fully visible ground and submersible connection for temporary or permanent parking of 600 A deadbreak connectors that conform to IEEE Std 386™-2006 standard.

All standoff bushing brackets have a stainless steel eyebolt with a brass pressure foot. The bushing body is bolted to a stainless steel base bracket using a stainless steel bolt. Special pins ensure firm location of the bushing on the bracket.

Installation

A clampstick tool is used to place the standoff bushing in the parking stand on the front plate of the apparatus. Special tools are required to thread de-energized 600 A connectors onto the standoff bushing. Refer to the appropriate connector catalog section or installation instruction for further clarification. Refer to *Service Information S600-24-1 15, 25, and 35 kV Class Insulated Standoff Bushing Installation Instructions* for complete installation details on the insulated standoff bushing. For installation of the grounded standoff bushing, refer to *Service Information S600-24-2 15, 25, and 35 kV Class Grounded Standoff Bushing Installation Instructions* for details.

EATON

Powering Business Worldwide




Figure 1. Grounded standoff bushing on left is made of aluminum alloy and has five feet of insulated cable. Insulated bushing on right is molded of epoxy insulation material.

Note: Dimensions given are for reference only.




Figure 2. Standoff bushing stacking dimensions.

Production tests (insulated standoff bushing)

Tests conducted in accordance with IEEE Std 386™-2006 standard:

- ac 60 Hz 1 Minute Withstand
 - 50 kV
- Minimum Corona Voltage Level
 - 26 kV

Tests conducted in accordance with Eaton requirements:

- Physical Inspection
- Periodic Dissection
- Periodic Fluoroscopic Analysis

Table 1. Voltage Ratings and Characteristics — Insulated Standoff Bushing

Description	kV
Standard Voltage Class	35
Maximum Rating Phase-to-Ground	21.1
ac 60 Hz 1 Minute Withstand	50
dc 15 Minute Withstand	103
BIL and Full Wave Crest	150
Minimum Corona Voltage Level	26

Voltage ratings and characteristics are in accordance with IEEE Std 386™-2006 standard.

Table 2. Current Ratings and Characteristics — Grounded Standoff Bushing

Description	Amperes
Short Time	25,000 A rms symmetrical for 0.17s

Current ratings and characteristics are in accordance with IEEE Std 386™-2006 standard.

Ordering information

To order a 35 kV Standoff Bushing Kit, refer to Table 3.

Each kit contains:

- Standoff Bushing with Bracket
- Shipping Cap (not for energized operation)
- Installation Instruction Sheet

Existing insulated or grounded bushing can be converted for use with T-OP™ II connectors by ordering and installing the copper alloy T-OP II stud.**

****If a T-OP II STUD (STUD-T) is installed in an existing insulated or grounded bushing the short end of the stud must be threaded into the bushing.**

****The T-OP II STUD (STUD-T) should only be used when grounding or achieving a visible break of a T-OP II termination.**

Table 3. Ordering Selection Guide

Example: To order Copper Insulated Bushing with Copper Stud Loose (Shown Below)
 Catalog Number would be I SB635 C S C

← Standard → | ← Options →

Digits: 1 2 3 4 5 6

I **SB635** **C** **S** **C** —

Digit 1	Description
G	For Grounded Bushing***
I	For Insulated Bushing

Digit 2	Given
	SB635

Digit 3	Description
A	For Aluminum Bushing***
C	For Copper Bushing*

Digit 4 & 5	Description
S A	Aluminum Stud
S T	T-OP II Stud
S C	Copper Stud
Leave Blank	No Stud Required

Digit 6	Description
P	Stud Permanently Installed
Leave Blank	Bagged Stud, Loose in Box
Leave Blank	No Stud Required

* Eaton recommends when a copper standoff is designated – use only copper stud or T-OP II stud.
 *** Grounded bushing available in solid wrought aluminum alloy only. Digit 3 will be "A".

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

Eaton's Cooper Power Systems Division
2300 Badger Drive
Waukesha, WI 53188
United States
Eaton.com/cooperpowerseries

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. CA650057EN

Eaton, Cooper Power, and T-OP are valuable trademarks of Eaton in the U.S. and other countries. You are not permitted to use these trademarks without the prior written consent of Eaton.
IEEE Std 386™-2006 standard are trademarks of the Institute of Electrical and Electronics Engineers, Inc., (IEEE). This publication is not endorsed or approved by the IEEE.

For Eaton's Cooper Power series standoff bushings product information call 1-877-277-4636 or visit: www.eaton.com/cooperpowerseries.