


1 VersaPanel



The VersaPanel is a high performance IP44 LED 600x600 flat panel luminaire that offers significant energy and maintenance savings.

Sleek minimalist design, the VersaPanel is a direct equivalent to a traditional fluorescent solution with reduced energy consumption.

Suitable for a wide range of applications where cost effective slim line lay-in solution is desired.

- Even lit appearance
- Easy to clean IP44 wipeable surface
- 3532 lumen output
- 4000K colour temperature options
- Simple installation, low profile lay-in solution with plug/socket driver connection
- Efficacy of 97.5 Llm/cW
- ENEC driver, DALI option

Light Engine and Control Gear Options

- 4000K high output, high efficiency optimised LED panel illumination, >80CRI
- Fixed output LED driver (ENEC) as standard
- Emergency, 3hr duration option available


Materials

- Housing back plate – steel
- Panel frame – extruded aluminium in white finish
- Panel optic – polystyrene

Installation Notes

- Suitable for exposed ‘T’ ceilings, lay-in installation
- Remote driver on plug and socket connection
- Mains connection is direct to the driver as standard
- The luminaire panels are IP44 rated. Please note the driver and gearbox are IP20 rated

Dimensions - LED Panel




Weight (kg)	Depth (mm)
2.28	8

Specification

To specify state; Flat panel edge lit LED, IP44 rated, with diffuse opal panel, extruded aluminium in white finish, plug/socket connection mains to ENEC driver (IP20) as Eaton’s VersaPanel range, part no _____

Photometric Data

Cat. No: VSTPP66374KZ



LOR 100%
DLOR 100%
ULOR 0%
SHR max 1:1.46
SHR nom 1-1.25

Utilisation factors / TM5

Reflectances			Room index								
C	W	F	0.75	1	1.25	1.5	2	2.5	3	4	5
0.7	0.5	0.2	56	67	74	79	87	92	95	100	103
0.7	0.3	0.2	48	59	66	72	80	86	90	96	99
0.7	0.1	0.2	42	53	61	67	75	81	86	92	96
0.5	0.5	0.2	54	64	71	77	84	88	92	96	99
0.5	0.3	0.2	47	58	65	70	78	84	87	92	96
0.5	0.1	0.2	42	52	60	66	74	79	84	89	93
0.3	0.5	0.2	53	63	69	74	81	85	88	92	95
0.3	0.3	0.2	47	57	64	69	76	81	85	89	92
0.3	0.1	0.2	42	52	59	65	72	78	82	87	90
0	0	0	40	49	56	61	69	74	78	82	86
BZ-class			5	5	5	5	5	5	5	5	5

See page 468 for design guide

Catalogue Numbers

Cat No	Description	Max Wattage (W)	Lumen output	Efficiency (lm/cw)	Colour Temperature °K	Weight	Power Factor
VSTPP66374KZ	VersaPanel LED 3532lm 4000K	36	3532	97.5	4000K	2.28Kg	>.95
VST60SMK	VersaPanel LED surface mount box	-	-	-	-	1.60Kg	-

For emergency option add characters EL in from of the Cat No, example VSTPP66344KZ becomes ELVSTPP66344KZ

For DALI option replace characters KZ with DD example VSTPP66344KZ becomes VSTPP66344KDD

DALI Emergency option would be ELVSTPP66344DD

For more information on the installation requirements and product specifications, please visit our website: <https://uk.eaton.com/content/gb/en/products/product-catalog/VersaPanel-recessed.html>