

DESCRIPTION

The HALO™ LED Vapor tight Floodlight provides an indoor/outdoor solution in applications where lighting fixture protection is required. The fixture provides equivalent light output up to 100-watt incandescent and 23-watt CFL fixtures, with high-quality and long lasting illumination. The fixture is vapor tight to protect against dust and moisture. Ideal for garages, storage, and industrial areas.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Construction

- Durable die-cast aluminum housing and cage provides protection against vandalism
- Vapor tight IP65 rating protects against dust and moisture
- Versatile mounting options – Wall, Ceiling and Post
- Frosted glass lens
- (5) 1/2 NPT Conduit openings

Electrical

- Maintenance-free LEDs with L70 50,000 hours of life
- Universal 120-277V power supply
- Fixture operating temperature range from -20°C to 40°C
- cULus listed for wet locations

Optics

- 3500K color temperature
- Fixture produces up to 1450 Lumens

Warranty


- 5 year limited warranty




LED VAPOR TIGHT FLOODLIGHT

DIMENSIONS

Top View



Side View



ORDERING INFORMATION

Model	Description
VT1730	Die-Cast Aluminum Vapor tight LED
VT1730IH	Die-Cast Aluminum Vapor tight LED


CERTIFICATION DATA

cULus Wet Location Listed
Lighting Facts® Approved

TECHNICAL DATA

-20°C to 40°C Temperature Rating
Wall, Ceiling, and Post Mount

PHOTOMETRICS



		.25 Fc Coverage Area					
		8'		10'		15'	
Model Number	Lumens	X	Y	X	Y	X	Y
VT1730	1450	15	34	15	36	14	37
VT1730IH	1450	15	34	15	36	14	37

Technical Information

Model Number	Description	Voltage (V)	Power (W)	Delivered Lumens	Efficacy (Lum/Watt)	LED Color Temperature (K)	CRI
VT1730	LED Vapor tight Floodlight	120-277V	17.7	1450	82	3500K	80
VT1730IH	LED Vapor tight Floodlight	120-277V	17.7	1450	82	3500K	80