

Britesign 2



Using the latest in LED technology Britesign 2 has been remodelled to suit most prestigious installations and commercial interiors. It has an ultra low profile of 40mm and the stepped bezel creates an even slimmer appearance which makes this LED exit sign blend unobtrusively into almost any environment. The picture frame style die cast aluminium bezel is available in satin anodised finish as well as the ever popular white and houses a 33m viewing distance legend panel. The 50,000 hour long life LED source provides outstanding savings in lamp replacement and maintenance costs when compared to a traditional 8W lamp.

- ICeL registered with verified light performance
- Ultra low profile design
- 50,000 hour LED source for minimum maintenance
- EN1838 compliant legend panel
- Bezel colour options on request
- Self-contained, slave, self-test and addressable testing options
- Available in self-contained, AC/DC and AC mains slave versions

Lamp Options

- High intensity 3W white LED strip


Materials

- Housing - steel, powder coated in RAL9016 finish
- Bezel - die cast aluminium, satin anodised or powder coated in RAL9016 finish
- Legend panel - clear acrylic with screen print legend
- Batteries - (self contained versions) - NiCd

Installation Notes

- Suitable for wall mounting
- First fix body with rear BESA entry and 20mm conduit entry on top face
- Direct fix via keyhole slots
- Bezel assembly screwed securely to base
- Supplied with LED strip

Dimensions



Options


- Bezel choice of satin anodised aluminium and powder coat white finish
- Central system slave version
- CeaGuard testing version
- CGLine+ addressable testing (see page 237)
- EasiCheck addressable testing

Specification

Self-contained - To specify state: 40mm deep, ultra low profile exit sign utilising 50,000 hour LED light source. Legend illumination to be fully compliant with requirements of EN 1838 and retained by die cast aluminium bezel as Britesign 2 range part no. _____

Self-Test/Slave - To specify state: Intelligent self testing/Static inverter compatible slave 40mm deep, ultra low profile exit sign utilising 50,000 hour LED light source. Legend illumination to be fully compliant with requirements of EN 1838 and retained by die cast aluminium bezel as Britesign 2 range part no. _____

Maximum Viewing Distance



Catalogue Numbers

System Mode	White Finish	Aluminium Finish	Weight (kg)
Maintained 3Hr	BS2M	BS2MA	1.45
Maintained 3Hr self-test	BS2MIS	BS2MAIS	1.50
Maintained 3Hr EasiCheck	BS2MEC	BS2MAEC	1.50
Maintained 3Hr EasiCheck 2	BS2MEC2	BS2MAEC2	1.50
230V CeaGuard Slave	BS2S230CG	BS2SA230CG	1.25
230V AC Mains Slave	BS2S230	BS2SA230	1.25
230V AC Mains Slave EasiCheck	BS2S230EC	BS2SA230EC	1.30

CGLine+

Maintained 3Hr	BS2MCGL	BS2MACGL	1.45
----------------	---------	----------	------

Legend Panel	Euro Pictogram	Cat No	ISO Pictogram	Cat No	Weight (kg)
Up arrow		BSAU		BSAU-ISO	0.8
Down arrow		BSAD		BSAD-ISO	0.8
Left arrow		BSAL		BSAL-ISO	0.8
Right arrow		BSAR		BSAR-ISO	0.8