

CERTIFICATE

Issued to:
Applicant:
EATON; CEAG Notlichtsysteme GmbH
Senator-Schwartz-Ring 26
59494 Soest, Germany

Licensee:
EATON; CEAG Notlichtsysteme GmbH
Senator-Schwartz-Ring 26
59494 Soest, Germany

Product : Luminaires for emergency lighting with LED light source
Trade name(s) : EATON, EATON JSB or EATON MENVIER
Type(s)/model(s) : Atlantic LED CGLine+ and Outdoor Wall CGLine+

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 60598-1:2015, EN 60598-1:2015/AC:2016, EN 60598-1:2015/AC:2015, EN 60598-2-22:2014, EN 60598-2-22:2014/AC:2015, EN 60598-2-22:2014/AC:2016-05, EN 60598-2-22:2014/AC:2016-09 and EN 60598-2-24:2013
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 990758

DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration of the ENEC certification agreement and under the conditions of the ENEC certification agreement.

This certificate is issued on 26 March 2018 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-103151

DEKRA Certification B.V.



drs. G.J. Zoetbrood
Managing Director



Henk Schendstok
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Luminaires for emergency lighting with LED light source
Trade name(s)	: EATON, EATON JSB or EATON MENVIER
Type(s)/model(s)	: Atlantic LED D 1-8h/D CGLine+, Atlantic LED D 1-8h/D CGLine+ H, Atlantic LED O 1-8h/D CGLine+, Atlantic LED O 1-8h/D CGLine+ H, Atlantic LED R 1-8h/D CGLine+, Atlantic LED R 1-8h/D CGLine+ H, Atlantic LED S 1-8h/D CGLine+, Atlantic LED S 1-8h/D CGLine+ H, Outdoor Wall 1-8h/D CGLine+ and Outdoor Wall 1-8h/D CGLine+ H
Rated voltage / nature of supply	: 230 Vac
Rated frequency	: 50/60 Hz
Rated input power	: 7 W or 9,3 W
Rated wattage (LED)	: 2 x 1,6 W
Classification	: Class I
Degree of protection	: IP65
Ambient temperature ranges	: ta = -20 °C...35 °C (with heater) ta = 5 °C...35 °C (without heater)

TESTS**Test requirements**

EN 60598-1:2015
EN 60598-1:2015/AC:2016
EN 60598-1:2015/AC:2015
EN 60598-2-22:2014
EN 60598-2-22:2014/AC:2015
EN 60598-2-22:2014/AC:2016-05
EN 60598-2-22:2014/AC:2016-09
EN 60598-2-24:2013

Test result

The test results are laid down in DEKRA test file 222440800.

Additional information

The luminaires contain a LED module with is in compliance with EN 62031:2008 + A1:2013 + A2:2015 (tested as part of the appliance).

The luminaire also comply with the D-marking requirements according EN 60598-2-24:2013

This certificate replaces certificate No. 71-102717 which we herewith declare invalid.

The list of components is laid down at test report 2224408.54.

Conclusion

The examination proved that all requirements were met.

Factory locations

EATON; CEAG Notlichtsysteme GmbH
Senator-Schwartz-Ring 26
59494 Soest, Germany

SC Cooper Industries Romania SRL
Zona Industrială Vest
Str. III, Nr. 12
310510 Arad, Romania