

GHG26 disconnect switches

For harsh & hazardous areas

Features:

- Explosion protected factory sealed motor circuit switches
- Innovative break-line in cover allows full wiring access, making installation quick and easy
- High impact enclosure is designed for excellent corrosion resistance and will not warp from hot or cold water
- Tongue-in-groove seal guarantees IP66 rating and eliminates possibility of accidental opening or leakage
- Lockable handle meets OSHA lockout/tagout requirements
- Molded-in-place mounting feet provide a water channel between wall and enclosure
- Large rotary handle provides easy gripping with gloved hands
- Captive cover screws prevent water exposure and possible corrosion



Materials:

- Enclosure - 10A: Impact-resistance thermoplastic; 20A – 180A: fiberglass-reinforced polyester
- Enclosure gasket – silicone
- Handle – impact-resistant thermoplastic
- Cover screws – stainless steel
- Conduit entries: zinc Myers hubs

Certifications & compliances:

- cCSAus Certified
- Class I, Division 2, Groups A, B, C, D
- Class I, Zones 1 and 2, AEx de IIC, T6
- Class II, Division 1, Groups E, F, G (CSA)
- Class II, Division 2, Groups F, G
- ATEX Approved - PTB
- Ex de IIC, T6, Zones 1 and 2A, IP66
- GOST-R and GOST-K
- CSA Standard: C22.2 No.14
- NEMA 4X
- IP66

	10 Amp	20 Amp	40 Amp		
Pole	3 Pole	3 Pole	6 Pole	3 Pole	6 Pole
Rated Voltage	500 V	690 V	690 V	690 V	690 V
Auxiliary Contact	1 NO, making – lagging breaking – leading	1 NO, making – lagging breaking – leading	1 NC	1 NO, making – lagging breaking – leading	1 NC
Auxiliary Connection	14 AWG 2 x 2.5 mm ²	12 AWG 2 x 4 mm ²	12 AWG 2 x 4 mm ²	12 AWG 2 x 16 mm ²	12 AWG 2 x 16 mm ²
Connection Terminals	14 AWG	12 AWG	12 AWG	6 AWG	6 AWG
Conduit Entries	1 x 3/4"	2 x 3/4"	2 x 3/4"	2 x 3/4"	2 x 1"
Part number	GHG 261 0005 L0002	GHG 262 2301 L0003	GHG 262 2601 L0002	GHG 263 2301 L0002	GHG 263 0050 L0002
Weight	0.55 kg/1.2 lbs.	1.5 kg/3.3 lbs.	2.3 kg/5.1 lbs.	2.3 kg/5.1 lbs.	6.5 kg/14.3 lbs.
Wall Mounting Plate	GHG 610 1953 R0101	GHG 610 1953 R0104	GHG 610 1953 R0118	GHG 610 1953 R0118	not required


Switches can be mounted directly onto a wall. The optional wall mounting plate offers a more convenient method of mounting.



Powering Business Worldwide

	80 Amp		125 Amp		180 Amp	
Pole	3 Pole	6 Pole	3 Pole	3 Pole	3 Pole	3 Pole
Rated voltage	690 V	690 V	690 V	690 V	690 V	690 V
Auxiliary contact	1 NO, making – lagging breaking – leading	1 NC	1 NO, making – lagging breaking – leading	1 NO, making – lagging breaking – leading	1 NO, making – lagging breaking – leading	1 NO, making – lagging breaking – leading
Auxiliary connection	12 AWG 2 x 50 mm ²	12 AWG 2 x 50 mm ²	12 AWG 1 x 70 mm ²	12 AWG 1 x 70 mm ²	12 AWG 1 x 120 mm ²	12 AWG 1 x 120 mm ²
Connection terminals	2 AWG	2 AWG	2/0 AWG	2/0 AWG	4/0 AWG	4/0 AWG
Conduit entries	2 x 1-1/2"	2 x 1-1/2"	2 x 1-1/2"	2 x 1-1/2"	2 x 2"	2 x 2"
Part number	GHG 264 0020 L0017	GHG 264 0021 L0002	GHG 265 0010 L0003	GHG 265 0010 L0003	GHG 266 0006 L0002	GHG 266 0006 L0002
Weight	6.5 kg/14.3 lbs.	9.0 kg/19.8 lbs.	16.0 kg/35.2 lbs.	16.0 kg/35.2 lbs.	16.5 kg/36.3 lbs.	16.5 kg/36.3 lbs.
Wall mounting plate	not required	not required	not required	not required	not required	not required

Dimensions



Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

Eaton's Crouse-Hinds
1201 Wolf Street
Syracuse, NY 13208
Crouse-Hinds.com

© 2019 Eaton
All Rights Reserved
Printed in USA
Publication No. 5436-1219
December 2019

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.