

Putting it all together

Features

R9000EE

Bussed Termination Enclosures:


- For termination of power utility supply cables
- Pad lockable
- 100-1200 Ampere

R1124HEE

Bussed Gutter: Intended for use as a distribution point for multiple load applications.

R11 Series

- 400-1200 Ampere.
- Unique "Clover leaf" knockouts allow for easy installation of all TB units without the need for conduit
- Load lugs pre-installed - one set per meter position



R10 Series

- 400-2000 Ampere
- 2-10 foot lengths

121413

20 Ampere, Current Transformer Rated With Test Switch Provision:

- For use with separate CT enclosure
- Add prefix "W" for pre-wired, installed test switch

127TB

TB Series (safety socket):

- For commercial applications
- 100-200 Ampere
- Available with main breakers, fusible pull-outs and load center combinations

303611RTCT

Utility/Current Transformer Enclosures:


- Designed to house current transformers 400-800 Ampere, bussed current transformer mounting bases
- Hinged covers available on HRTCT series

6067HA

- Stud/Stud, Lug/Lug, and Lug/Stud configurations
- 10K and 50KAIC rating
- For use with bar type CT that meet ANSI C12.11

Benefits

- Labor saving, simple design
- Versatile installation
- Smaller footprint
- Perfect for strip mall and other commercial applications



Powering Business Worldwide

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. SA307002EN
July 2015 BA151MTR

B-Line Division
509 West Monroe Street
Highland, IL 62249
United States
Phone: 800-851-7415

cooperline.com/metering

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

