

Commercial Meter Pedestals - Pad Mounted, Dual Distribution



Application

- Utility meter, main disconnect and distribution panel
- Receive ANSI C12.10 watthour meters

Construction

- Ring type
- NEMA Type 3R
- ANSI 61 gray E-coat finish
- Separate sealable utility termination and meter compartments
- Padlockable disconnect and distribution section
- Underground feed


Standards

- UL Listed
- ANSI C12.7

Accessories

- 5th jaw kit - 50365 (single phase)
- Filler plate kit - 25139
- Class T fusible pullouts
- Controls, see page 109

Catalog Number	Amp Rating	Jaws	Service Type	Bypass	Distribution		Mounting Pad
					Voltage	Main Breaker Branch Circuits	
CMP4911M	100	4	1Ø, 3W	--	240	50A/2P (2)	
CMP4911MC	100	4	1Ø, 3W	TB	240	50A/2P (2)	
CMP4911MCH	100	4	1Ø, 3W	TB	480	50A/2P (2)	
CMP4914M	100	7	3Ø, 4W	--	240	50A/3P (2)	
CMP4914MC	100	7	3Ø, 4W	TB	240	50A/3P (2)	
CMP4914MCH	100	7	3Ø, 4W	TB	240	50A/3P (2)	Per
CMP4921M	200	4	1Ø, 3W	--	240	100A/2P (2)	Customer
CMP4921MC	200	4	1Ø, 3W	TB	240	100A/2P (2)	Specification
CMP4921MCH	200	4	1Ø, 3W	TB	480	100A/2P (2)	
CMP4924M	200	7	3Ø, 4W	--	240	100A/3P (2)	
CMP4924MC	200	7	3Ø, 4W	TB	240	100A/3P (2)	
CMP4924MCH	200	7	3Ø, 4W	TB	480	100A/3P (2)	
CMP4941MN	400	4	1Ø, 3W	MCC	240	400A/2P (2)	



Data subject to change without notice. Consult local utility for area acceptance. All dimensions are in inches.

Commercial Meter Pedestals - Specials



CMP4012MC-1

Application

- Utility meter, main disconnect and distribution panel
- Receive ANSI C12.10 watthour meters

Construction

- Ring type
- NEMA Type 3R
- ANSI 61 gray E-coat finish
- Separate sealable utility termination and meter compartments
- Padlockable disconnect and distribution section
- Underground feed

Standards

- UL Listed
- ANSI C12.7

Accessories

- 5th jaw kit - 50365 (single phase)
- Filler plate kit - 25139
- Class T fused pullouts
- Controls, see page 109

Commercial
Meter Pedestals

Pad Mount, Dual Metered Side-by-Side - Fig. 1 (see page 116)

Catalog Number	Amp Rating	Jaws	Service Type	Bypass	Distribution				Mounting Pad	Dimensions		
					Voltage	Main Breaker	Branches	Type		Width	Depth	Height
CM2P4111MC-1	200	7	1Ø,3W	TB	240	100A,2P	12	Plug-In	MB3215	32"	17 ¹ / ₂ "	54"
				TB	240	100A,2P	12	Plug-In				
CM2P4411MC-1	200	7	1Ø,3W	TB	480	100A,2P	14	Bolt-On	MB3215	32"	17 ¹ / ₂ "	54"
				TB	480	100A,2P	14	Bolt-On				
CM2P4121MC-1	400	4	1Ø,3W	MCC	240	200A,2P	--	--	MB3215	32"	17 ¹ / ₂ "	54"
				MCC	240	200A,2P	--	--				
CM2P4421MC-1	400	7	3Ø,4W	TB	240	200A,2P	12	Plug-In	MB3215	32"	17 ¹ / ₂ "	54"
				TB	240	200A,2P	12	Plug-In				




Pad Mount, Dual Metered - Fig. 2 (see page 116)

Catalog Number	Amp Rating	Jaws	Service Type	Bypass	Distribution				Mounting Pad	Dimensions		
					Voltage	Main Breaker	Branches	Type		Width	Depth	Height
CMP4012MC-1	100	4	1Ø,3W	--	240	60A,2P	4	Plug-In	MB1515	15"	17 ¹ / ₂ "	54"
				TB	240	60A,2P	4	Plug-In				
CMP4022MC-1	100	4	1Ø,3W	--	240	60A,2P	4	Plug-In	MB1515	15"	17 ¹ / ₂ "	54"
				TB	240	60A,2P	12	Plug-In				

Pad Mount, Split Load Style - Fig. 3 (see page 116)

Catalog Number	Amp Rating	Jaws	Service Type	Bypass	Distribution				Mounting Pad	Dimensions		
					Voltage	Main Breaker	Branches	Type		Width	Depth	Height
CMP4011SLC-1	100	4	1Ø,3W	TB	240	60A,2P	4	Plug-In	MB1515	15"	17 ¹ / ₂ "	54"
			Unmetered	1Ø,3W	Unmetered	240	60A,2P	4				

Commercial Meter Pedestals - Specials



Commercial Meter Pedestals

Data subject to change without notice. Consult local utility for area acceptance. All dimensions are in inches.