

# CT Mounting Bases

## Test Switch Configuration Sheet

### Application

- Current transformer metering
- Customizable configurations

### Construction

- BMC mounting base
- Tin and nickel plating
- Color coded handles

### Standards

- UL Recognized component
- ANSI C12.9



Name \_\_\_\_\_

Company Name \_\_\_\_\_

Address \_\_\_\_\_

Phone \_\_\_\_\_

Email \_\_\_\_\_



Poles

### Configuration

	1	2	3	4	5	6	7	8	9	10
Switch (KS, SH, CN, TB, X)										
Bussing (B, S)										
Ganged Handles (Y, N)										
Barrier (Y, N)										
Handle Color (R, B)										
45° Stops (Y, N)										

### Special Features

Cover	<input type="checkbox"/>	Yes	<input type="checkbox"/>	No				
Base Size	<input type="checkbox"/>	7 Pole	<input type="checkbox"/>	10 Pole				
No. of Poles	<input type="checkbox"/>	4	<input type="checkbox"/>	7	<input type="checkbox"/>	10	<input type="checkbox"/>	Other
Plating	<input type="checkbox"/>	None	<input type="checkbox"/>	Tin	<input type="checkbox"/>	Nickel		

### Keys

#### Switches

KS	SH	CN	TB	X
Knife Switch	Knife Switch with shunt	Current Switch with Test Jack	Thru Bar	Unused Space

#### Bussing

<b>B</b>	Bypass
<b>S</b>	Short

#### Handle Color

<b>R</b>	Red
<b>B</b>	Black

- Other options and arrangements are available. Please contact the factory for a full product line.
- Test Switched are available mounted and wired. Contact factory for details.

For online form, see [www.cooperblinemetring.com](http://www.cooperblinemetring.com).

Send completed form to customer service at Eaton's B-Line Business. See address information on back cover.

Data subject to change without notice. Consult local utility for area acceptance. All dimensions are in inches.