

DC/DC converter for railway applications

JL & JLH open frame version



Description

Originally designed for on-board passenger information systems, the JL series is now available in a wide variety of input and output configurations. Capable of providing 35W, 50W or 60W* of continuous power at ambient temperatures of up to 75°C, the low component count makes the JL series a highly reliable yet cost-effective solution. For applications where the converter will be housed within an enclosure, the open frame version offers a further cost saving. The JL and JLH series have recently expanded to include alternative size footprints, connectors and functional features.

Special features include:

Input specifications

- Wide operating temperature range
- · Low component count, high reliability
- Simple construction open frame or enclosed versions available
- · Low cost

JL series family-overview

JL versions rectangular PCB with enclosure option

JLR versions include RIA12 and other functional options

JLM versions mini PCB footprint with enclosure option

JLM M1 versions mini PCB footprint with conduction cooled package

All versions as above; JLH, JLHM

60Watts* JLHM option '/2'

*New versions: JLM & JLHM M1 Conduction cooled versions

*New versions: JLR & JLHR series with functional options and to RIA12

The following input voltages versions are available as standard:

110V (66.0 - 137.5V) dc (Suffix A)
72V (50.0 - 90.0V) dc (Suffix D)
52V (36.0 - 65.0V) dc (Suffix C)
36V (25.0 - 50.4V) dc (Suffix F)
24V (16.8 - 33.6V) dc (Suffix B)

Options for JLR and JLHR versions

Code	Detail
L	Output OK Relay (NO and NC)
R	RIA12 filtering
V	Enable. Connect to + input to enable

Parameter	Detail		
Input Ripple	EN50155		
Input Protection Reverse polarity protection. Surges and transients to EN50155 (Direct and Indirect)			
Inrush Current	ush Current Limited to typically 5 x nominal current (after 0.1ms)		
Efficiency	85% typical		
Hold up time	10ms to EN50155 S2 (including input short)		
Supply change over (dips)	0 - 6Un 100mS to EN50155 Class C1		



Output specifications

Parameter	Detail	
Maximum Output Power	35W JL, JLR, JLM, versions 50W JLH, JLHR, JLHM versions 60W* JLHM option '/2'	
Output Versions	Single	
Output Voltage	Fixed output can be specified from 5V to 110Vdc (5Vdc output versions limited to 35Watts)	
Setting Tolerance	±2%	
Line / Load Regulation	±2%	
Temperature Coefficient	<0.02% / °C	
Output Ripple	<1% Pk-Pk of Output Voltage	
Output Noise	<75mV Pk-Pk superimposed (up to 20MHz)	
Response Time	1.0ms to within 2% (for a 20% - 90% load change)	
Current Limit	Operates at approximately 115% of rated current	
Isolation (tested at dc equivalent voltage)	Input to Output 2.0kV ac Output/Input to Case 1.0kV ac (enclosed version)	

^{* -} Limited availability - consult factory for further details

Environmental details

Parameter	Detail
Operating Temperature	-25°C to +75°C (no derating)
Storage Temperature	-40°C to +80°C
Cooling	By convection (M1 versions have conduction cooled package)
Relative Humidity	95% max.
Shock & Vibration	EN50155 (EN61373)

Applicable norms

Parameter	Detail
EMC	EN50155 (2017), EN50121-3-2 (2016)
Other	EN50155 (2017) RIA 12(version specific)

JL & JLH enclosed version



JLM & JLHM open frame version



Mechanical characteristics

Parameter	Detail				
Construction	Open fram	e PCB with I	Enclosure options		
	Version		PCB Footprint	Enclosed version	
Dimensions	JL & JLH		220x73x30mm	250x78x35mm	
(Length x Width x	JLR & JLF	IR	220x73x30mm	250x78x35mm	
Height)	JLM & JL	HM	115x85x23mm	145x91x35mm	
	JLM M1 (cooled	Conduction	135x85x30mm with base plate		
Finish	PCB, Conformal coating. Enclosure, plated mild steel.				
Weight	<0.5kg	<0.5kg			
	Version	Input Con	nector	Output Connector	
Connections	JL & JLH	Wago 236-	501	Wago 236-501	
	JLR & JLHR	Wago 236-501 or Wago 721-434		Wago 236-501 or Wago 721-435	
	JLM & JLHM	(standard) Wago 236-501 (Q4 option) Wago 721-433/001-000 (Q6 option) Wago 236-501 (Q1 option) 3W3 male power D-type		Wago 721-434/001-000 Wago 721-433/001-000 Wago 236-501 3W3C coded female power d-type	

Options for all series

Code	Detail
T	Extended temperature range; -40°C operating
S	Enclosure with DIN Rail mounting clips
S2	Enclosure no clips

Options for JLM & JLHM series only

Code	Detail
M1	Conduction cooled package
Q1	Power d-type connectors
Q4	Alternative Wago input connector (input & output both cage clamp)
Q6	Alternative Wago output connector (input & output both pluggable)

JLM & JLHM enclosed version



Eaton EMEA Headquarters Route de la Longeraie 7 1110 Morges, Switzerland

© 2018 Eaton All Rights Reserved Publication No. PAXXXXXXXXE / CSSC-281 October 2021

Eaton Electrical Products Ltd

Glebe Farm Technical Campus Knapwell, Cambridge, CB23 4GG United Kingdom Tel: +44 (0)1954 267726 MartekUKsales@eaton.com

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.









