


Direct Check Valve Module

(F3) DGMDC-5-T-X-*-20




Cracking Pressure (bar)	Spring
0.35	595980
4.00	595981

Model	Body S/A	Diagram Plate	Spacer
DGMDC-5-P-Y-*-260	595964	627231	—
DGMDC-5-T-X-*-260	595965	630310	595967

▲Service all units with
F3 Seal Kit 920247

Model Code



1 Seal Material F3 - Seals for mineral oil and fire resistant fluids	4 Port Operated Upon P -Pressure ("Y" Models only) T - Tank port ("X" Models only)	6 Cracking Pressure L - 0.35 bar (5 PSI) T - 4.00 bar (58 PSI)
2 Model Series DGMDC - Modular valve Direct check	5 Direction of Check Funtion X - Free flow from load Y- Free flow in	7 Design
3 Interface 02 - NFPA-D 3 - CETCP		

For satisfactory service life of these components, use full flow filtration to provide fluid which meets ISO cleanliness code 18/15 or cleaner. Selections from Eaton OFP,OFR and OFRS filter series are recommended.

Printed in U.S.A.