

# Check Valves




## Pressure Operated Check Valve Module with Decompression Feature

DGPC-06-DA\*DB\*-51

DGPC-01-DA\*DB\*-51

### Model Code




<b>1 Seals</b> Seals for mineral oil and fire resistant fluids	<b>4 Port Size</b> 1/8 inch	<b>8 Decompression Feature</b>
<b>2 Model Series</b> Directional control gasket mounted	<b>5 Decompression Feature</b>	<b>9 Check Valve Location</b> Cylinder port 'B'
<b>3 Model Series</b> Pressure operated check module	<b>6 Check Valve Location</b> Cylinder port 'A'	<b>10 Check Valve Cracking Pressure</b> Cylinder port 'B' standard 30 PSI (Omit for standard)
	<b>7 Check Valve Cracking Pressure</b> Cylinder port 'A' standard 30 PSI (Omit for standard)	<b>11 Design</b>

● Included in 347456 S/A

**NOTE**  
 Refer to installation drawing 522650 for bolt kit information and module stacking data. The mounting bolt torque should not exceed a maximum of 112 lb. in.

- 345288 Plate
- 342224 Seat (2 req'd)

- 352439 Spring (2 req'd)
- 342225 Check Valve (2 req'd)
- 347325 Piston
- ▲ 262334 "O" Ring (5 req'd)



▲ Included in 920215 F3 Seal Kit

# Model Code

(F3) - DG PC - 06 - D A \* D B \* - 51

┌───┐
┌───┐
┌───┐
┌───┐
┌───┐
┌───┐
┌───┐
┌───┐
┌───┐
┌───┐
┌───┐

1
2
3
4
5
6
7
8
9
10
11

<p><b>1 Seals</b> Seals for mineral oil and fire resistant fluids</p>	<p><b>4 Port Size</b> 3/4 inch</p>	<p><b>8 Decompression Feature</b></p>
<p><b>2 Model Series</b> Directional control gasket mounted</p>	<p><b>5 Decompression Feature</b></p>	<p><b>9 Check Valve Location</b> Cylinder port 'B'</p>
<p><b>3 Model Series</b> Pressure operated check module</p>	<p><b>6 Check Valve Location</b> Cylinder port 'A'</p>	<p><b>10 Check Valve Cracking Pressure</b> Cylinder port 'B' standard 30 PSI (Omit for standard)</p>
	<p><b>7 Check Valve Cracking Pressure</b> Cylinder port 'A' standard 30 PSI (Omit for standard)</p>	<p><b>11 Design</b></p>

