

 COOPER POWER SYSTEMS DIVISION COMPONENTS & PROTECTIVE EQUIPMENT	TIME-CURRENT CHARACTERISTIC CURVES MINIMUM MELT 15.5kV ELSP BACKUP TYPE OIL IMMERSIBLE CURRENT FUSE
	Tests made at LOW Volts ac at HIGH pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1981 (R1992) MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE PLUS THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.
DRAWN BY: SKS DATE: 07-17-97 REPLACES: 07/92/REV 02/REG NO. 17661 DWG NO.: 42 38646 B 00	COOPER COOPER POWER SYSTEMS DIVISION COMPONENTS & PROTECTIVE EQUIPMENT DRAWN BY: SKS DATE: 07-17-97 REPLACES: 07/92/REV 02/REG NO. 17661 DWG NO.: 42 38646 B 00

Reference Data
 R240-91-65
 Page 1 of 2



 COOPER POWER SYSTEMS DIVISION COMPONENTS & PROTECTIVE EQUIPMENT	TIME-CURRENT CHARACTERISTIC CURVES MAXIMUM CLEAR 15.5kV ELSP BACKUP TYPE OIL IMMERSIBLE CURRENT FUSE
	Tests made at RATED Volts ac at LOW pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1981 (R1992) MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE MINUS THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.
DRAWN BY: SKS DATE: 07-17-97 REPLACES: 07/92/REV 02/REG NO. 17661 DWG NO.: 42 38646 B 00	COOPER COOPER POWER SYSTEMS DIVISION COMPONENTS & PROTECTIVE EQUIPMENT DRAWN BY: SKS DATE: 07-17-97 REPLACES: 07/92/REV 02/REG NO. 17661 DWG NO.: 42 38646 B 00

Reference Data
 R240-91-65
 Page 2 of 2