


 COOPER POWER SYSTEMS DIVISION COMPONENTS & PROTECTIVE EQUIPMENT	<b>TIME-CURRENT CHARACTERISTIC CURVES</b> MINIMUM MELT 23.0kV ELSB BACKUP TYPE OIL IMMERSIBLE CURRENT LIMITING FUSE	
	DRAWN BY: <b>EKS</b> <b>CKWD</b> DATE: <b>07-17-97</b> DATE: REPLACES: <b>07/92/REV 02</b> REG. NO. <b>17661</b> DWG. NO.: <b>42 38648 B 00</b>	Tests made at LOW Volts ac at HIGH pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1981 (R1992) MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE PLUS THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.

Reference Data  
 R240-91-68  
 Page 1 of 2



 COOPER POWER SYSTEMS DIVISION COMPONENTS & PROTECTIVE EQUIPMENT	<b>TIME-CURRENT CHARACTERISTIC CURVES</b> MAXIMUM CLEAR 23.0kV ELSB BACKUP TYPE OIL IMMERSIBLE CURRENT LIMITING FUSE	
	DRAWN BY: <b>EKS</b> <b>CKWD</b> DATE: <b>07-17-97</b> DATE: REPLACES: <b>07/92/REV 02</b> REG. NO. <b>17661</b> DWG. NO.: <b>42 38648 B 00</b>	Tests made at RATED Volts ac at LOW pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1981 (R1992) MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE MINUS THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.

Reference Data  
 R240-91-68  
 Page 2 of 2