

Relief Valves



Multi-Pressure Relief Valve


CG/CS/CT-06-**(*)-(V)-DG8BL-M(***)-M-**-*-30

CG/CS/CT-10-**(*)-(V)-DG8BL-M(***)-M-**-*-30



WARNNG

Use only a DG4V-3-8BL-M-**-40-S288 directional valve as a pilot for this relief valve. Use of a different pilot can block relief valve, causing excessive system pressure.



Model	Cover Spring	Pressure Range PSI-(bar)
C*-**-B	2280	125-1000 (8.5-70)
C*-**-C	583937	500-2000 (35-140)
C*-**-F	2281	1500-3000 (105-210)

Model	Screw (4 Req'd)	Torque		L'Washer 4 (Req'd)
		lb.ft.	N.m	
C*-06	1036	11-15	14.9-20.3	68907
C*-10	1076	35-43	47.5-58.3	68909

***Note**


Coat 292230 Adj. Screw, 283949 Lockscrew and 1485 Locknut with oil prior to assembly.

⊖ This part used at final test to obtain correct pressure range.



Model	"O" Ring	Seat	Hydro Cone	Lo-Vent Spring	Hi-Vent Spring	Cover
C*-06	262361	343153	343154	2077	184458	370664
C*-10	262367	283954	283952	291822	291821	370669

Note: Use either a Lo-Vent or Hi-Vent Spring.
Do not use both. See Model Code.

Sectional Head 1 Inoperative



Section "E" Vent Head 2 or 3




Part	Kit	Part	Kit
1485	944064	226816	944071
1649	944067	227405	944074
AX-36212	944053	292230	944072
64520	944068	326317	944073
113000	944055	329463	944041
160571	944069	343740	944038
218750	944070		

Parts with available only in kits of 25.
Reference kit on parts order.


Model	◆ Body	
	-06	-10
CG-	580456	581703
CS-	581701	580430
CT-	590348	590300

- Available only in Kits of 25
- ▲ Included in F3-06 Seal Kit 919684
- Δ Included in F3-10 Seal Kit 919685
- ◆ Not available for sale



Model Code

F3 - C * - ** - ** - (V) - DG -8BL - M - M - W - B - 30



1 Seal Material

F3 - Seals for mineral oil and fire resistant fluids

2 Model Series

CGST - Relief valve, subplate, straight thread, NPTF thread

3 Nominal Size

06 - 3/4"
10 - 1 1/4"

4 Pressure Range Head 1, 2 or 3

	PSI	Bar
B	125-1000	(8, 5-70)
C	500-2000	(35-140)
F	1500-3000	(105-210)
E	Vent	

5 Spring

V - Hi vent spring
Omitted - Lo vent spring

6 Directional Valve

7 Spool Type & Spring Arrangement

DG4V-3-8BL-M(P**)-**-*-40
(Refer to I-3863-S for detailed service information)

8 Flag Symbol Heading

Electrical features and options

9 DG4V-3 Pivot Valve & Adapter Plate

10 Wiring Housing

1/2" NPT thread

11 Coil Identification Letter

(Refer to I-3862-S)

12 Design

For satisfactory service life of these components in industrial applications, use full flow filtration to provide fluid which meets ISO cleanliness code 20/18/15 or cleaner. Selections from Eaton OFP, OFR, and OFRS series are recommended.