

150 A series multiple (dual voltage) switch cap/wrench, lever or hotstick operable handles installation instructions



Powering Business Worldwide

DISCLAIMER OF WARRANTIES AND LIMITATION OF LIABILITY

The information, recommendations, descriptions and safety notations in this document are based on Eaton Corporation's ("Eaton") experience and judgment and may not cover all contingencies. If further information is required, an Eaton sales office should be consulted. Sale of the product shown in this literature is subject to the terms and conditions outlined in appropriate Eaton selling policies or other contractual agreement between Eaton and the purchaser.

THERE ARE NO UNDERSTANDINGS, AGREEMENTS, WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING WARRANTIES OF FITNESS FOR A PARTICULAR PURPOSE OR MERCHANTABILITY, OTHER THAN THOSE SPECIFICALLY SET OUT IN ANY EXISTING CONTRACT BETWEEN THE PARTIES. ANY SUCH CONTRACT STATES THE ENTIRE OBLIGATION OF EATON. THE CONTENTS OF THIS DOCUMENT SHALL NOT BECOME PART OF OR MODIFY ANY CONTRACT BETWEEN THE PARTIES.

In no event will Eaton be responsible to the purchaser or user in contract, in tort (including negligence), strict liability or otherwise for any special, indirect, incidental or consequential damage or loss whatsoever, including but not limited to damage or loss of use of equipment, plant or power system, cost of capital, loss of power, additional expenses in the use of existing power facilities, or claims against the purchaser or user by its customers resulting from the use of the information, recommendations and descriptions contained herein. The information contained in this manual is subject to change without notice.

Contents

SAFETY INFORMATION

Safety Information	iv
--------------------------	----

PRODUCT INFORMATION

Introduction	1
Acceptance and Initial Inspection	1
Handling and Storage	1
Standards	1

GENERAL MOUNTING DESCRIPTION

Torque requirements	1
Clearance	1
Mechanical strength	1
Electrical Ratings	1

OPERATION INSTRUCTIONS	2
------------------------------	---

MOUNTING SEQUENCE	3
-------------------------	---

DIMENSIONS	7
------------------	---



Safety for life



Eaton meets or exceeds all applicable industry standards relating to product safety in its Cooper Power™ series products. We actively promote safe practices in the use and maintenance of our products through our service literature, instructional training programs, and the continuous efforts of all Eaton employees involved in product design, manufacture, marketing, and service.

We strongly urge that you always follow all locally approved safety procedures and safety instructions when working around high voltage lines and equipment, and support our “Safety For Life” mission.

Safety information

The instructions in this manual are not intended as a substitute for proper training or adequate experience in the safe operation of the equipment described. Only competent technicians who are familiar with this equipment should install, operate, and service it.

A competent technician has these qualifications:

- Is thoroughly familiar with these instructions.
- Is trained in industry-accepted high and low-voltage safe operating practices and procedures.
- Is trained and authorized to energize, de-energize, clear, and ground power distribution equipment.
- Is trained in the care and use of protective equipment such as arc flash clothing, safety glasses, face shield, hard hat, rubber gloves, clampstick, hotstick, etc.

Following is important safety information. For safe installation and operation of this equipment, be sure to read and understand all cautions and warnings.

Hazard Statement Definitions

This manual may contain four types of hazard statements:

DANGER

Indicates an imminently hazardous situation which, if not avoided, will result in death or serious injury.

WARNING

Indicates a potentially hazardous situation which, if not avoided, could result in death or serious injury.

CAUTION

Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury.

CAUTION

Indicates a potentially hazardous situation which, if not avoided, may result in equipment damage only.

Safety instructions

Following are general caution and warning statements that apply to this equipment. Additional statements, related to specific tasks and procedures, are located throughout the manual.

DANGER

Hazardous voltage. Contact with hazardous voltage will cause death or severe personal injury. Follow all locally approved safety procedures when working around high- and low-voltage lines and equipment.

G103.3

WARNING

Before installing, operating, maintaining, or testing this equipment, carefully read and understand the contents of this manual. Improper operation, handling or maintenance can result in death, severe personal injury, and equipment damage.

G101.0

WARNING

This equipment is not intended to protect human life. Follow all locally approved procedures and safety practices when installing or operating this equipment. Failure to comply can result in death, severe personal injury and equipment damage.

G102.1

WARNING

Power distribution and transmission equipment must be properly selected for the intended application. It must be installed and serviced by competent personnel who have been trained and understand proper safety procedures. These instructions are written for such personnel and are not a substitute for adequate training and experience in safety procedures. Failure to properly select, install or maintain power distribution and transmission equipment can result in death, severe personal injury, and equipment damage.

G122.3

Product information

Introduction

Eaton's Cooper Power™ series 150 A externally operated single-, two-, and three-phase dual voltage switches are designed for use in distribution transformers filled with transformer oil, Envirottemp™ FR3™ fluid, or an approved equivalent. They are designed for use in pole- or pad-mounted transformers. The switches are used to connect primary windings in series for higher winding ratios or parallel for a lower voltage winding ratio.

Read This Manual First

Read and understand the contents of this manual and follow all locally approved procedures and safety practices before installing or operating this equipment.

Additional Information

These instructions cannot cover all details or variations in the equipment, procedures, or process described nor provide directions for meeting every possible contingency during installation, operation, or maintenance. For additional information, contact your Eaton representative.

Acceptance and initial inspection

Each dual voltage switch is in good condition when accepted by the carrier for shipment. Upon receipt, inspect the shipping container for signs of damage. Unpack the dual voltage switch and inspect it thoroughly for damage incurred during shipment. If damage is discovered, file a claim with the carrier immediately.

Handling and storage

Be careful during handling and storage of the dual voltage switch to minimize the possibility of damage. If the switch is to be stored for any length of time prior to installation, provide a clean, dry storage area.

Standards

ISO 9001 Certified Quality Management System

General mounting description

Torque Requirements

To Seal - 80-120 inch pounds.

Clearance

Table 1. Dielectric Clearance Dimensions

kV BIL	Minimum mounting clearance under-oil to Gnd/ between phases/and depth below top level
95	1.1"
125	1.5"
150	2.5"

Mechanical—External handle clear of obstructions. When the lever handle with index plate is used, flattening for the gasket sealing surface must not exceed a depth of .25".

Mechanical Strength

Designed to support leads sized per rating of switch. Standard dielectric dimensions for lead separation should be followed. Connection of leads can be made either to bolt tabs or crimped into connectors (if supplied). Special stationary contact with crimp barrels are available for #16-14, #12-10, #8, and #6 copper wires. Bolt tab designed to accept 1/4"-20 bolt and ring tongue terminals through #4. A larger terminal may be used if the terminal amperage rating corresponds with the switch rating.


CAUTION

Equipment Damage. Caution should be used in lead training [dressing] to avoid lead forces of over 60 pounds on the switch in any direction. Anticipate thermal expansion and contraction as well as mechanical stresses from transportation, which will vary by application. Misuse of lead training could result in equipment damage.

Electrical Ratings


Impulse Withstand	150 kV BIL
60 Hz 1 Minute Withstand	50 kV
Continuous Current	150 A rms Series Position 300 A rms Parallel Position

OPERATION INSTRUCTIONS




Cap/Wrench

It is keyed for one way in/ one way out when fully switching to ensure positive switch contact.



The molded arrow on the switch shaft must line up with the molded arrow inside the wrench.

The white molded arrow on the interior of the cap points to the switched position.



Lever or Hotstick Handles

Lever or point of rigid hotstick handle points to the switched position. To switch, back out lock screw, rotate to desired position, turn in lock screw to ensure positive switch contact.

WARNING

Enclosed "Warning" decals (P/N 1139089A01 and P/N 1139090A01) must be displayed at or near operating handle of switch as a warning to service personnel. Failure to do so will constitute a waiver of all warranty and indemnity obligations which may be attributable to Eaton.

WARNING

The misapplication of the switch constitutes a potential hazard to life and property. Accordingly, the user must exercise due care in utilizing these instructions to assure that the switch is properly applied.

The decals included with the handle kit are to be located on the tank wall near the switch operating handle as a warning to service personnel (see Figure 1).

Failure to do so will constitute a waiver of all warranty and indemnity obligations attributable to Eaton.

Cap/Wrench Switches

WARNING

**DE-ENERGIZE TRANSFORMER
BEFORE CHANGING VOLTAGE.**

**REMOVE PROTECTIVE CAP AND USE KEY ON
END TO OPERATE SWITCH, REPLACE CAP
BEFORE ENERGIZING.**

 COOPER Power Systems

1139089A01

Lever or Hotstick Handle Switches

WARNING

**DE-ENERGIZE TRANSFORMER
BEFORE CHANGING VOLTAGE.**

**BEFORE OPERATING HANDLE, BACK OUT
LOCKSCREW TO CLEAR INDEX PLATE. AFTER
CHANGING SWITCH POSITION, TURN IN LOCKSCREW
SECURELY BEFORE ENERGIZING AGAIN.**

 COOPER Power Systems

1139090A01

Figure 1. Warning decals.

Mounting sequence




Figure 2. Cap/wrench assembly. (Exploded view)




Figure 3. Cap/wrench assembly.

Note: See Table 2 for dimensions A-D.




Figure 4. Hotstick handle assembly. (Exploded view)







Figure 5. Three-phase with hotstick handle assembly.

Note: See Table 2 for dimensions A-D.

Figure 6. Single-phase (with back deck)—hotstick handle assembly.

Note: See Table 2 for dimensions A-D.




Figure 7. Three-phase with lever handle assembly. (Exploded view)

Note: See Table 2 for dimensions A-D.

Table 2. Tap Changer Mounting Sequence (All configurations).

Switch Dimensions in/mm

Figure	A	B	C
Figure 2	1.7 (43.0 mm)	3.30 (83.8 mm)	2.36 (60.0 mm)
Figure 4	3.46 (88.0 mm)	9.12 (232.0 mm)	3.0 (76.0 mm)
Figure 5	3.46 (88 mm)	5.71 (145.0 mm)	3.0 (76.0 mm)
Figure 6	1.6 (40.0 mm)	9.12 (232.0 mm)	3.0 (76.0 mm)

"A" Dimensions All Switch Configurations in/mm

Contact Type	"D" in/mm
Bolt Tabs for 1/4 inch Bolts	5.52 (140.0 mm)
16-14 AWG Terminals	
12-10 AWG Terminals	6.63 (168.0 mm)
8 AWG Terminals	
6 AWG Terminals	6.88 (175.0 mm)

Note: Switch can be used on 14 gauge to .25 inch thick frontplate.

Contact your Eaton representative for other switch configurations.




Figure 8. Switch mounting hole.



Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

**Eaton's Cooper Power Systems
Division**
2300 Badger Drive
Waukesha, WI 53188
United States
Eaton.com/cooperpowerseries

EATON
Powering Business Worldwide

© 2016 Eaton
All Rights Reserved
Printed in USA
Publication No. MN800012EN Rev 00
(Replaces S800721 Rev. 01)

Eaton is a registered trademark.

All trademarks are property
of their respective owners.

For Eaton's Cooper Power series product
information call 1-877-277-4636 or visit:
www.eaton.com/cooperpowerseries.