

200 A 25 kV class insulated standoff bushing



General

Eaton's Cooper Power™ series 200 A, 25 kV insulated standoff bushing meets the full requirements of IEEE Std 386™-2006 standard – Separable Insulated Connector Systems and provides a single loadbreak interface made of high quality peroxide-cured EPDM rubber. It is used to isolate and sectionalize energized cable in pad-mounted cabinets, underground vaults, and other apparatus. Temporary or permanent parking of energized 200 A, 15.2/26.3 kV loadbreak elbow connectors that conform to IEEE Std 386™-2006 standard is simplified with use of the insulated standoff bushing.

The insulated standoff bushing is designed to be installed in the parking stand mounted on a transformer or other apparatus. A grounding lug is provided on the standoff bushing bracket for attachment of a drain wire to ensure deadfront construction. When mated with a comparably rated product, the insulated standoff bushing provides a fully-shielded, submersible, separable connector for energized operation.

The standard insulated standoff bushing has a stainless steel eyebolt with a brass pressure foot. The molded peroxide-cured EPDM rubber body is bolted to a stainless steel base bracket using a galvanized steel holddown ring. A completely stainless steel bracket assembly is available for extremely corrosive environments.

Installation

No special tools are required. A clampstick tool is used to place the standoff bushing in the parking stand on the front plate of the apparatus. Refer to *Service Information S500-22-1, 200 A 15, 25, and 35 kV Class Insulated Standoff Bushing Installation Instructions* for details.

EATON

Powering Business Worldwide

Production tests

Tests conducted in accordance with IEEE Std 386™-2006 standard:

- AC 60 Hz 1 Minute Withstand
 - 40 kV
- Minimum Corona Voltage Level
 - 19 kV

Tests conducted in accordance with Eaton requirements:

- Physical Inspection
- Periodic Dissection
- Periodic X-ray Analysis

Ordering information

To order the 25 kV Insulated Standoff Bushing Kit, refer to Table 2.

Each kit contains:

- Insulated Standoff Bushing with Bracket
- Shipping Cap (not for energized operation)
- Installation Instruction Sheet

Table 2. Standoff Bushing Kit

Description	Catalog Number
Standoff Bushing with Standard Bracket	ISB225
Standoff Bushing with Stainless Steel Bracket	ISB225S

Table 1. Voltage Ratings and Characteristics

Description	kV
Standard Voltage Class	25
Maximum Rating Phase-to-Ground	15.2
AC 60 Hz 1 Minute Withstand	40
DC 15 Minute Withstand	78
BIL and Full Wave Crest	125
Minimum Corona Voltage Level	19

Voltage ratings and characteristics are in accordance with IEEE Std 386™-2006 standard.

Eaton
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
 Eaton.com

Eaton's Cooper Power Systems Division
 2300 Badger Drive
 Waukesha, WI 53188
 United States
 Cooperpower.com

© 2015 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. CA650004EN

Eaton and Cooper Power are valuable trademarks of Eaton in the U.S. and other countries. You are not permitted to use these trademarks without the prior written consent of Eaton.
 IEEE Std 386™-2006 standard is a trademark of the Institute of Electrical and Electronics Engineers, Inc., (IEEE). This publication is not endorsed or approved by the IEEE.

For Eaton's Cooper Power series insulated standoff bushing product information call 1-877-277-4636 or visit: www.cooperpower.com.

