

Wi-Fi smart duplex receptacle

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:



WFTRCR15



Description

2-Pole, 3-wire grounding
15A, 125V/AC, 60Hz, 1/2 HP

- Set up and control receptacle using the Amazon Alexa App or by voice commands
- No hub required
- LED indicator system alerts if the device is not set up in the network
- Preset whether your device comes on or stays off following a power outage
- Adjust how long lights stay on to allow for a safe, convenient exit
- Neutral required for installation
- Dimmable white LED indicator illuminate to indicate ON/OFF status
- Provides control of one outlet leaving the other one for normal use
- One outlet can be controlled with a single pole switch
- Rated for 1/2 HP motor loads
- For added safety, complies with NEC specification that states all receptacles installed in dwelling units must be tamper resistant

Table 1. Wi-Fi smart duplex receptacle

Catalog No.	Description	Color suffix
<input type="checkbox"/> WFTRCR15_	Wi-Fi smart duplex receptacle	B, BK, GY, LA, RB, SG, V, W

Compliances, specifications and availability are subject to change without notice.



Powering Business Worldwide

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Applications

Eaton's Wi-Fi smart duplex receptacle replaces regular receptacles to provide local and remote ON/OFF control of a single outlet. The receptacle can be remotely controlled and the user can create routines, schedules and group devices using the Amazon Alexa App. Ideal for controlling floor lamps, appliances and holiday lights, the receptacle makes controlling your home easier.


Table 2. Specifications

Catalog No.	WFTRCR15
Performance	Maximum amperage for receptacle is 15A Rating: 125V/AC, 60Hz Horsepower rating: 1/2 HP
Installation & Programming	Please reference the Instruction Sheet included with the product for wiring installation. For programming of the device, see the Quick Start Guide
Testing & Code Compliance	cULus Listed Appliance Control 38DS. Tested per UL244B, UL498 and UL498B. NOM Certified. Complies with FCC part 15, class B.
Terminations	Receptacles have four screw terminals for line, neutral, ground and 3-way
Material Characteristics	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: 32°F to 104°F (0°C to 40°C)
Warranty	2-year limited product warranty

Table 3. Color Ordering Information

For ordering devices, include Catalog No. followed by the Color Suffix: B (Brown), BK (Black), GY (Gray), LA (Light Almond), RB (Oil Rubbed Bronze), SG (Silver Granite), V (Ivory), W (White).

Color options:



Product Dimensions






Figure 1. WFTRCR15

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Single Location Control Installation



Two Location Control Installation using a 3-Way Switch



Certifications & Compliances

Catalog No.	cULus	NOM 426	FC
WFTRCR15	•	•	•

KEY: cULus cULus NOM 426 NOM FC FCC


Related Products

Wi-Fi smart products



WACD, WFSW15, WFD30

Wallplates



PJS26, PJS262

Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/smarthome

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/smarthome

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlan Km 17.8 s/n
Col. Villa Jardin esq.
Cerrada 8 de Mayo
Cuautitlan, Mexico CP 54800
Mexico
Eaton.mx
Eaton.com/smarthome