

## HX open distribution cutouts installation instructions



## **DISCLAIMER OF WARRANTIES AND LIMITATION OF LIABILITY**

The information, recommendations, descriptions and safety notations in this document are based on Eaton Corporation's ("Eaton") experience and judgment and may not cover all contingencies. If further information is required, an Eaton sales office should be consulted. Sale of the product shown in this literature is subject to the terms and conditions outlined in appropriate Eaton selling policies or other contractual agreement between Eaton and the purchaser.

THERE ARE NO UNDERSTANDINGS, AGREEMENTS, WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING WARRANTIES OF FITNESS FOR A PARTICULAR PURPOSE OR MERCHANTABILITY, OTHER THAN THOSE SPECIFICALLY SET OUT IN ANY EXISTING CONTRACT BETWEEN THE PARTIES. ANY SUCH CONTRACT STATES THE ENTIRE OBLIGATION OF EATON. THE CONTENTS OF THIS DOCUMENT SHALL NOT BECOME PART OF OR MODIFY ANY CONTRACT BETWEEN THE PARTIES.

In no event will Eaton be responsible to the purchaser or user in contract, in tort (including negligence), strict liability or otherwise for any special, indirect, incidental or consequential damage or loss whatsoever, including but not limited to damage or loss of use of equipment, plant or power system, cost of capital, loss of power, additional expenses in the use of existing power facilities, or claims against the purchaser or user by its customers resulting from the use of the information, recommendations and descriptions contained herein. The information contained in this manual is subject to change without notice.

# Contents

## SAFETY INFORMATION

Safety Information .....	iv
--------------------------	----

## PRODUCT INFORMATION

Introduction .....	1
Acceptance and initial inspection .....	1
Handling and storage .....	1
Standards .....	1

## INSTALLATION INSTRUCTIONS

Mounting cutout or disconnect .....	2
Installing fuse holder or disconnect blade .....	2
Fuse link breaking .....	3
Loadbreaking device .....	3
Cutout-arresters .....	3
Installing fuse links in 100 A fuseholder .....	4
Installing fuse links in 200 A fuseholder .....	5

MAINTENANCE .....	5
-------------------	---



## Safety for life



Eaton meets or exceeds all applicable industry standards relating to product safety in its Cooper Power™ series products. We actively promote safe practices in the use and maintenance of our products through our service literature, instructional training programs, and the continuous efforts of all Eaton employees involved in product design, manufacture, marketing, and service.

We strongly urge that you always follow all locally approved safety procedures and safety instructions when working around high voltage lines and equipment, and support our “Safety For Life” mission.

## Safety information

The instructions in this manual are not intended as a substitute for proper training or adequate experience in the safe operation of the equipment described. Only competent technicians who are familiar with this equipment should install, operate, and service it.

A competent technician has these qualifications:

- Is thoroughly familiar with these instructions.
- Is trained in industry-accepted high and low-voltage safe operating practices and procedures.
- Is trained and authorized to energize, de-energize, clear, and ground power distribution equipment.
- Is trained in the care and use of protective equipment such as arc flash clothing, safety glasses, face shield, hard hat, rubber gloves, clampstick, hotstick, etc.

Following is important safety information. For safe installation and operation of this equipment, be sure to read and understand all cautions and warnings.

### Hazard Statement Definitions

This manual may contain four types of hazard statements:

#### DANGER

Indicates an imminently hazardous situation which, if not avoided, will result in death or serious injury.

#### WARNING

Indicates a potentially hazardous situation which, if not avoided, could result in death or serious injury.

#### CAUTION

Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury.

#### CAUTION

Indicates a potentially hazardous situation which, if not avoided, may result in equipment damage only.

### Safety instructions

Following are general caution and warning statements that apply to this equipment. Additional statements, related to specific tasks and procedures, are located throughout the manual.

#### DANGER

**Hazardous voltage. Contact with hazardous voltage will cause death or severe personal injury. Follow all locally approved safety procedures when working around high- and low-voltage lines and equipment.**

G103.3

#### WARNING

**Before installing, operating, maintaining, or testing this equipment, carefully read and understand the contents of this manual. Improper operation, handling or maintenance can result in death, severe personal injury, and equipment damage.**

G101.0

#### WARNING

**This equipment is not intended to protect human life. Follow all locally approved procedures and safety practices when installing or operating this equipment. Failure to comply can result in death, severe personal injury and equipment damage.**

G102.1

#### WARNING

**Power distribution and transmission equipment must be properly selected for the intended application. It must be installed and serviced by competent personnel who have been trained and understand proper safety procedures. These instructions are written for such personnel and are not a substitute for adequate training and experience in safety procedures. Failure to properly select, install or maintain power distribution and transmission equipment can result in death, severe personal injury, and equipment damage.**

G122.3



## CAUTION

---

**The HX Cutout is designed to be operated in accordance with normal safe operating procedures. These instructions are not intended to supersede or replace existing safety and operating procedures. The HX cutout should be installed and serviced only by personnel knowledgeable of good safety practices and fully trained on the installation and application of HX cutout fuses. Refer to ANSI® Standard C37.48 and NEMA® SG-2 for guidelines in operating and maintaining this equipment. These standards should be followed in addition to this instruction and instruction for fuse holders.**

---

## Product information

### Introduction

Eaton's Cooper Power™ series HX cutouts can be quickly and economically adapted to double current rating or higher interrupting ratings as load and system capacity increases dictate. Simple blade changeout makes 300 A disconnects out of HX design. Fuseholders and blades are only stock items required for this broad versatility.

### Read this manual first

Read and understand the contents of this manual and follow all locally approved procedures and safety practices before installing or operating this equipment.

### Additional information

These instructions cannot cover all details or variations in the equipment, procedures, or process described nor provide directions for meeting every possible contingency during installation, operation, or maintenance. For additional information, contact your Eaton representative.

### Acceptance and initial inspection

Each cutout is in good condition when accepted by the carrier for shipment. Upon receipt, inspect the shipping container for signs of damage. Unpack the cutout and inspect it thoroughly for damage incurred during shipment. If damage is discovered, file a claim with the carrier immediately.

### Handling and storage

Be careful during handling and storage of the cutout to minimize the possibility of damage. If the cutout is to be stored for any length of time prior to installation, provide a clean, dry storage area.

### Quality standards

ISO 9001 Certified Quality Management System

## Installation instructions

### Mounting cutout or disconnect

#### Step 1

##### Inspect porcelain

- Before mounting the cutout, make sure the porcelain is not cracked or chipped.
- Do not install a cutout if any hardware is loose, bent, distorted or out of alignment.

#### Step 2

##### Mount cutout

- Mount the cutout on a suitable mounting bracket.
- Position the lock washers. See Figure 1.

**Note:** DO NOT mount this cutout in vaults or other enclosed areas. Ionized gases are generated during fault clearing operations and may cause electrical flash in enclosed spaces.




Figure 1. Cutout mounting.

#### Step 3

##### Position Cutout

- Pivot the cutout in a position that will provide ease of operation, maximum electrical clearance and venting clearance before securely tightening the carriage bolt nut.

## Installing fuse holder or disconnect blade

### CAUTION

Only qualified personnel should operate and inspect an open cutout. Such personnel should observe company safety procedures and wear protective equipment. Operator should be positioned away from the exhaust path when closing cutout.

#### Step 1

##### Insert switchstick hook

- Insert the hook of the switchstick into the lifting loop. The fuse holder or blade will hang on the hook in a position to be installed.

#### Step 2

##### Guide fuse holder

- Guide the fuse holder lower casting trunnion into the cutout hinge and disengage switchstick. Figure 2.





Figure 2. Attaching the fuse holder.

#### Step 3

##### Close fuse holder

- Place the hook of switchstick under the pull ring and swing the fuse holder to a 45° angle from the closed position.
- Then with head down and to one side of vent exhaust pattern, quickly and with a vigorous thrust on switchstick, push fuse holder to a closed position. Figure 3.



**Figure 3. Closing the fuse holder.**

#### Step 4

##### Remove switchstick

- Carefully remove switchstick from fuse holder to avoid pulling fuse holder open.



#### CAUTION

**Fuse holder should not be left hanging in the open position, as it may retain water.**

#### Cutout opening - breaking loads



#### WARNING


**Use proper load breaking devices to open energized cutouts. Injury and damage to cutout is possible if load-breaking devices are not used. When replacing damaged expendable CAPS they should be replaced with like expendable caps.**

Type "HX" cutout may be equipped with a permanent outdoor interrupter for breaking loads. Instructions for operating the "HX-CB" loadbreak are shown in *Service Information MN132011EN HX-CB Loadbreak Fuse Cutout Installation Instructions*, which is supplied with the loadbreak unit.

#### Fuse link breaking

The 100-ampere Type "HX" cutouts may be equipped with a linkbreak fuse holder and if so these instructions apply.

- Fuse links up to 100-ampere rating can be broken.
- Place the hook of switchstick on linkbreak arm.
- Pull sharply downward with a fast rapid motion. See Figure 4.



**Figure 4. Using the linkbreak.**

#### Loadbreaking device

The cutouts may be equipped with "hooks" for use with an approved loadbreak tool or other device designed for opening cutouts under load. Refer to the instructions with the device for their operation.

#### Cutout-arresters

Cutout-arrester combinations consist of a distribution arrester and HX cutout mounted on a common L bracket to be installed as a completed assembly. See Figure 5.

- During shipping and rough handling the units may get out of adjustment.
- Before mounting or during mounting, the arrester should be in same plane as the cutout with all nuts and bolts tight.



**Figure 5. Cutout-arrester combination.**

## Installing fuse links in 100 A fuseholder

### Step 1.

#### Remove cap/install link

- Remove cap and operated link. Replace link with appropriate rating in fuse tube.
- Make sure the contact button is secured on the fuse link and carefully straighten the fuse cable.

### Step 2.

#### Replace Cap

- Slide the straightened fuse link cable end into the fuse holder, replace and tighten the cap.

### Step 3.

#### Loosen thumb screw and depress flipper

- Loosen thumb screw and remove old cable. Install fuse cable under thumbscrew washer.
- Press flipper downward on the lower tube casting. Hold in this position for Step 4. See Figure 6.




Figure 6. Replacing the fuse link.

### Step 4.

#### Secure fuse link

- Dress fuse link cable around post on flipper and then around thumbscrew in a clockwise direction.
- Maintain tension on fuse link cable and with flipper firmly depressed, cross the fuse cable over itself and tighten the thumbscrew. See Figure 7.




Figure 7. Installing a new fuse link.

### Step 5.

#### Clip Excess Cable

- Clip excess fuse cable to within approximately 1/2" of the thumbscrew washer.



## Installing fuse links in 200 A fuseholder

---

### CAUTION

---

**Use only the ampere size and types of fuse links specified by your company**

---

#### Step 1.

##### Check fuse link

- Make sure the contact button is secured on the fuse link and carefully straighten the fuse cable.

#### Step 2.

##### Clamp Bolt Assembly

- Loosen the clamping bolt to raise the link clamp. Do not try to remove clamping bolt.

#### Step 3.

##### Remove cap

- Remove the cap from fuse holder and slide the straightened fuse link cable into the fuse tube and through the fuse cable box terminal, then replace the cap. See Figure 8.

---

### CAUTION

---

**Do not use 100 ampere or smaller fuse link in 200-ampere fuse holders. Such application could lead to failure of the cutout to clear fault currents. Replace operated or partially operated expendable caps with new expendable caps.**

---



Figure 8. Installing a fuse link in a 200 A fuse holder.

#### Step 4.

##### Secure fuse link

- With link clamp held down over the tube bore, pull the end of the fuse cable tightly and tighten clamping bolt. See Figure 9.



Figure 9. Secure fuse link leader..

#### Step 5.

##### Clip excess cable

- Clip excess fuse cable to within approximately 1/2" of the box terminal.

## Maintenance

Refer to IEEE Std C37.48™ standard, Guide for Application, Operation and Maintenance of High-Voltage Fuses, for maintenance of the HX Cutouts.

This page is intentionally left blank.

This page is intentionally left blank.



**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

**Eaton's Cooper Power Systems  
Division**  
2300 Badger Drive  
Waukesha, WI 53188  
United States  
Eaton.com/cooperpowerseries

**EATON**  
*Powering Business Worldwide*

© 2016 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. MN132012EN Rev: 00  
(Replaces KS010-01-1 Rev 00)

Eaton is a registered trademark.

All trademarks are property  
of their respective owners.

For Eaton's Cooper Power series product  
information call 1-877-277-4636 or visit:  
[www.eaton.com/cooperpowerseries](http://www.eaton.com/cooperpowerseries).