



NOTES:

- 1/ TYPE XB15 XENON BEACON
- 2/ CERTIFICATION DETAILS:
 UL/ULC LISTING No. E187894
 USL (USA): CLASS I, DIV. 2 GROUPS A, B, C & D
 CLASS II, DIV. 2 GROUPS F & G
 CLASS I, ZONE I, AExd IIC
 (Tamb. -67°F to +158°F)
 CNL (CANADA): CLASS I, DIV. 2 GROUPS A, B, C & D
 CLASS II, DIV. 2, GROUPS F & G
 CLASS I, ZONE I, Exd IIC
 (Tamb. -67°F to +158°F)
- 3/ AMBIENT TEMPERATURE RANGE: SEE TABLE
- 4/ WEIGHT - POLE MOUNT VERSION: 5.75±0.5lb
 DIRECT MOUNT VERSION: 6.5±0.5lb
- 5/ ENCLOSURE AND COVER MATERIAL: GLASS REINFORCED POLYESTER.
- 6/ OPTIONAL GUARD MATERIAL: STAINLESS STEEL WIRE OR CAST ALUMINIUM.
- 7/ OPTIONAL TAG/DUTY LABEL, LETTER SIZE 3/16" MAX.
- 8/ TERMINALS ARE SUITABLE FOR THE FOLLOWING:
 DIRECT MOUNT: 12-WAY, 440V, 25A 14AWG.
 PIPE MOUNT: 8-WAY, 440V, 25A 14AWG.
- 9/ CABLE ENTRIES:
 DIRECT MOUNT: UP TO 3 x 1/2" NPT OR 3 x 3/4" NPT
 ENTRIES IN POTISIONS 1, 2 & 3
 PIPE MOUNT: 1 x 1/2" NPT OR 1 x 3/4" NPT
- 10/ GENERAL TOLERANCE: 1/32"

TUBE ENERGY	T-RATING					
	+104°F / +40°C		+131°F / +55°C		+158°F / +70°C	
	Tg	Td	Tg	Td	Tg	Td
15J	T4	T135°C	T4	T135°C	T5	T100°C
10J	T4	T135°C	T5	T100°C	T6	T85°C
5J	T5	T100°C	T6	T85°C	T6	T85°C



EATON MEDC Ltd.
 UNIT B, SUTTON PARKWAY
 ODDICROFT LANE
 SUTTON-IN-ASHFIELD, NG17 5FB. U.K.
 Tel: +44 (0)1623 444400
 Web: WWW.COOPERMEDC.COM

DESIGNERS & MANUFACTURERS
 OF ELECTRICAL & ELECTRONIC
 EQUIPMENT & SYSTEMS
 FOR HAZARDOUS
 AREAS

ISSUES

B.01-12-17 PF

ALL DIMENSIONS ARE IN MILLIMETRES UNLESS OTHERWISE STATED

REMOVE ALL BURRS AND SHARP CORNERS

MACHINE SYMBOLS THUS ✓

THIS DRAWING IS CONFIDENTIAL AND IS THE PROPERTY OF MEDC AND MUST NOT BE REPRODUCED EITHER WHOLLY OR PARTLY. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHT ARE RESERVED

DRAWN BY: P.FISHWICK	DATE: 10/05/2013	TITLE: XB15 UL/ULC CUSTOMER GA	SHT 1 OF 1
CHECKED BY: D.COATES	DATE: 23/03/2015		
APPROVED BY: P.FISHWICK	DATE: 23/03/2015		
SCALE:1:2	A3	DWG NO. 276-472	REVISION B