

GuideLed SL 13061.1 CG-S

Emergency luminaire, ceiling recessed mounting



GuideLed SL 13061.1 CG-S

- Safety luminaire with LED technology for recessed mounting
- Unobtrusive, discrete appearance with round design and low installation depth of only 40 mm
- Conversion to square design with optional bezel to fit to the ceiling plan if necessary
- High spacing D50 classification and highly-efficient HighPowerLEDs
- Maintained or non-maintained operation programmable via STAR technology
- 80mm disc for 64-70mm ceiling cut out
- Minimum service requirement due to high service life of the LEDs (up to 50,000 hours)

GuideLed SL 13061.1 CG-S



Sqare bezel for GuideLed SL 130x1.1 CG-S




* Degree of protection - luminaire: IP41
Degree of protection - enclosure: IP20

Operation mode	Non-maintained
Certification	AS2293:2018, CISPR15:2017
Photometric classification	C0, C90: D50 (Refer to AS2293.1:2018 for luminaire spacing)
Luminous flux Φ_N	250 lm
Luminous flux Φ_E/Φ_N at end of rated operating time	100%
Housing material	PC, Aluminium
Housing colour	White RAL 9016
Weight	0.25 kg
Type of mounting	Recess mounting
Terminals	2 x 3 x 2,5 mm ² with flex and plug
Connection voltage	220 – 240 V AC, 50/60 Hz 176 – 275 V DC
Current consumption - 220 VDC operation	20 mA
Power consumption mains operation (apparent power/effective power)	8.0 VA / 3.9 W
Inrush current	1.5 A
Permissible ambient temperature	-20°C to +40°C
Light source	HighPower LED 1 x 2 W

Ordering details

Type	Scope of supply	Order No.
GuideLed SL 13061.1 CG-S	GuideLed SL 13061.1 CG-S, recessed mounting, D50 LED supply and CG-S technology come with flex and plug	40071354444
Sqare bezel	Sqare bezel GuideLed SL 130x1.1 CG-S	40071354488

Dimensions in mm



EATON

Powering Business Worldwide

Eaton

Cooper Electrical Australia Pty Ltd
10 Kent Road
Mascot NSW 2020

Tel: 1300 332 866
Fax: (02) 9693 1258
Email: safetyanz@eaton.com
www.eatoncorp.com.au
www.eaton.com