

CERTIFICATE

Issued to:
Applicant:
EATON; CEAG Notlichtsysteme GmbH
Senator-Schwartz-Ring 26
59494 Soest, Germany

Licensee:
EATON; CEAG Notlichtsysteme GmbH
Senator-Schwartz-Ring 26
59494 Soest, Germany

Product : CPS system for Emergency lighting
Trade name(s) : EATON, EATON CEAG, EATON JSB or EATON MENVIER
Type(s)/model(s) : LP-STAR

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard(s) EN IEC 62368-1:2020/A11:2020, EN IEC 62368-1:2020, EN IEC 62485-2:2018 and EN 50171:2001
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 990758


DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.

This certificate is issued on 3 March 2022 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-122856

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



H.R.M. Barends
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: CPS system for Emergency lighting
Trade name(s)	: EATON, EATON CEAG, EATON JSB or EATON MENVIER
Type(s)/model(s)	: LP-STAR
Rated current	: 5.5 A
Rated voltage/nature of supply	: 220-240 Vac
Rated frequency	: 50/60 Hz
Battery input voltage	: 19.2 - 28.8 Vdc
Output	: 220 - 240 V~, 50/60 Hz, 4.7 A, 1080 VA or 220 Vdc, 2.45 A, 540 W
Ambient temperature	: ta: 35 °C
Class	: class I
Degree of protection	: IP20
Overvoltage category	: II
Pollution degree	: 2
Connection to mains	: permanent connection

TESTS**Test requirements**

EN IEC 62368-1:2020/A11:2020
EN IEC 62368-1:2020
EN IEC 62485-2:2018
EN 50171:2001

Test result

The test results are laid down in DEKRA test file 225076100.

Additional information

The list of components is laid down in test report 2250761.50A.

Conclusion

The examination proved that all requirements were met.

Factory location

EATON; CEAG Notlichtsysteme GmbH
Senator-Schwartz-Ring 26
59494 Soest, Germany