

# CERTIFICATE

Issued to:  
Applicant:  
**Cooper Securite SAS**  
Parc Européen d'Entreprise RII Rue Beethoven -  
BP 10184  
63204 Riom, France

Licensee:  
**Cooper Securite SAS**  
Parc Européen d'Entreprise RII Rue Beethoven -  
BP 10184  
63204 Riom, France

Product : CGLine+ Web Compact Controller  
Trade name(s) : EATON, EATON CEAG, EATON Crompton, EATON JSB, EATON LUMINOX or EATON MENVIER  
Type(s)/model(s) : CTR160CGL2KS, CTR160CGL2KS-C, CTR160CGL2KS-G, CTR160CGL2KS-J, CTR160CGL2KS-L and CTR160CGL2KS-M

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard(s) EN IEC 62368-1:2020 and EN IEC 62368-1:2020/A11:2020
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 2193273


DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.


This certificate is issued on 30 September 2021 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-119465 REV.1

DEKRA Certification B.V.



B.T.M. Holtus  
Managing Director



H.R.M. Barends  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	: CGLine+ Web Compact Controller
Trade name(s)	: EATON, EATON CEAG, EATON Crompton, EATON JSB, EATON LUMINOX or EATON MENVIER
Type(s)/model(s)	: CTR160CGL2KS, CTR160CGL2KS-C, CTR160CGL2KS-G, CTR160CGL2KS-J, CTR160CGL2KS-L and CTR160CGL2KS-M
Model	: CGLine+ Web Compact Controller
Rated voltage/nature of supply	: 220-240 Vac
Rated frequency	: 50/60 Hz
Rated current	: 280 mA max
Rated input	: 34 W max
Class	: class II
Degree of protection	: IP20
Ambient temperature	: ta: 0...35 °C

**Product data – type CTR160CGL2KS**

Trade name : Eaton

**Product data – type CTR160CGL2KS-C**

Trade name : Eaton Crompton

**Product data – type CTR160CGL2KS-G**

Trade name : Eaton CEAG

**Product data – type CTR160CGL2KS-J**

Trade name : Eaton JSB

**Product data – type CTR160CGL2KS-L**

Trade name : Eaton Luminos

**Product data – type CTR160CGL2KS-M**

Trade name : Eaton Menvier

**TESTS****Test requirements**

EN IEC 62368-1:2020

EN IEC 62368-1:2020/A11:2020

**Test result**

The test results are laid down in DEKRA test file 225293300.



**Additional information**

This product also complies to EN 62034:2012

This certificate replaces certificate No. 71-119465 which we hereby declare invalid.

The list of components is laid down in test report 2252933.50A.

**Conclusion**

The examination proved that all requirements were met.

**Factory locations**

EATON; CEAG Notlichtsysteme GmbH  
Senator-Schwartz-Ring 26  
59494 Soest, Germany

SC Cooper Industries Romania SRL  
Zona Industrială Vest Str. III, Nr. 12  
310510 Arad, Romania

Cooper Securite SAS  
Parc Européen d'Entreprise RII Rue Beethoven - BP 10184  
63204 Riom, France