

# CERTIFICATE

Issued to:  
Applicant:  
**EATON; CEAG Notlichtsysteme GmbH**  
Senator-Schwartz-Ring 26  
59494 Soest, Germany

Licensee:  
**EATON; CEAG Notlichtsysteme GmbH**  
Senator-Schwartz-Ring 26  
59494 Soest, Germany

Product : Luminaires for emergency lighting with LED light source  
Trade name(s) : EATON, EATON JSB or EATON MENVIER  
Type(s)/model(s) : GuideLed SL CGLine+

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 60598-1:2015, EN 60598-1:2015/AC:2016, EN 60598-1:2015/AC:2015, EN 60598-2-22:2014, EN 60598-2-22:2014/AC:2015, EN 60598-2-22:2014/AC:2016-05 and EN 60598-2-22:2014/AC:2016-09
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 990758

DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration of the ENEC certification agreement and under the conditions of the ENEC certification agreement.

This certificate is issued on 26 March 2018 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-103148

DEKRA Certification B.V.



drs. G.J. Zoetbrood  
Managing Director



Henk Schendstok  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	: Luminaires for emergency lighting with LED light source
Trade name(s)	: EATON, EATON JSB or EATON MENVIER
Type(s)/model(s)	: GuideLed SL 13811 CGLine+, GuideLed SL 13812 CGLine+, GuideLed SL 13821 CGLine+, GuideLed SL 13822 CGLine+, GuideLed SL 13851 CGLine+ and GuideLed SL 13852 CGLine+
Rated input voltage / nature of supply	: 230 Vac
Rated frequency	: 50 / 60 Hz
Rated input power	: 6,7 W
Output power	: 2 x 1,6W
Degree of protection	: IP41 (module enclosure IP20)
Ambient temperature range (ta)	: ta = -5 °C...+30 °C (maintained) ta = 0 °C...+35 °C (non-maintained)

**Product data – type GuideLed SL 13811 CGLine+**

Classification	: Class II
Description	: recessed mounting

**Product data – type GuideLed SL 13812 CGLine+**

Description	: ceiling mounting
Classification	: Class I

**Product data – type GuideLed SL 13821 CGLine+**

Description	: recessed mounting
Classification	: Class II

**Product data – type GuideLed SL 13822 CGLine+**

Description	: ceiling mounting
Classification	: Class I

**Product data – type GuideLed SL 13851 CGLine+**

Description	: recessed mounting
Classification	: Class II

**Product data – type GuideLed SL 13852 CGLine+**

Description	: recessed mounting
Classification	: Class I

**TESTS****Test requirements**

EN 60598-1:2015  
EN 60598-1:2015/AC:2016  
EN 60598-1:2015/AC:2015  
EN 60598-2-22:2014  
EN 60598-2-22:2014/AC:2015  
EN 60598-2-22:2014/AC:2016-05  
EN 60598-2-22:2014/AC:2016-09

**Test result**

The test results are laid down in DEKRA test file 222440800.

**Additional information**

The luminaires contain a LED module which is in compliance with EN 62031:2008 + A1:2013 + A2:2015 (tested as part of the appliance).

This certificate replaces certificate No. 71-102714 which we herewith declare invalid.

The list of components is laid down at test report 2224408.50 and 2224408.51.

**Conclusion**

The examination proved that all requirements were met.

**Factory locations**

EATON; CEAG Notlichtsysteme GmbH  
Senator-Schwartz-Ring 26  
59494 Soest, Germany

SC Cooper Industries Romania SRL  
Zona Industrială Vest  
Str. III, Nr. 12  
310510 Arad, Romania