























- Unit with innovative LED technology certified family of emergency exit signs in accordance to EN 60598-2-22
- 3rd party certification
- Nickel Metal Hydride Batteries
- Push button for test operation
- Ceiling, wall, suspension, recessed and lateral installation
- Models of 30m and 40m visibility
- Test functions

#### **Light Source:**

LED Strip with a lifetime of more than 60,000 hours 24 LEDs producing 140 lumens

#### Materials:

Base and reflector unit in white Polycarbonate

#### Operation:

Maintained, slave and CBS models available

Autonomy from 3h

Adjustable brightness function to 50% in mains operation

Functional test button

Telecommand, Inhibition operation

Autotest and Slave models available

#### Installation:

Ceiling, wall, recessed, suspended through rope or metal pipe and lateral installation

No special tools required

## Applications:


Schools, universities, public administration, commercial environments

Hotels, restaurants, meeting rooms, offices, shops, cinemas, theaters, museums


Areas with large heights and long distance view requirements

# The Velos family of emergency lighting is designed and equipped with technical solutions that make it suitable for a wide range of applications. A complete range of accessories such as the recessed base for false ceiling installations, lateral and back base as well as suspension options allow for a variety of mounting positions.

Together with the choice of ISO and EURO exit sign labels, the Velos LED range is appropriate for emergency lighting requirements in multiple of places such as offices, restaurants, hotels, hospitals and general commercial applications.



### Viewing distance



Distance view of 30 / 40 meters provides the ability to use fewer products and less power consumption per coverage area of an application.



#### **Power Supply Unit**

- Easy to install with no use of special tools required.
  - · Environmentally friendly: no heavy metals and energy-optimized charging process due to low self-discharge.
- Easy to connect power cables via screwless connectors for up to 2.5mm<sup>2</sup> cables.
- Multiple entrance points for power cables through base and main body of the power supply unit.
  - Construction Material: Polycarbonate.
  - Large capacity NiMH batteries with small construction size for compact luminaire design.

#### 4 Velos electronics

- · Fully automatic function test (weekly) or duration test (every 10 weeks).
- Testing button for manual triggering of function test.
- Autotest models available with simple fault analysis with two LED indication of battery / LED test and status display (operation, function test, duration test, failure).
- Easily set the level in mains operation to 50% or 100%.
- Increased product reliability with LED matrix orientation. By groups of 3, if one of the 24 LEDs fails, the intact LEDs will illuminate more brightly.




# Velos Exit Sign

- Design life time: exceeding 60.000 hours lifetime expectancy using an EN1838 standard plate of 4mm thickness with 24 LED producing 140lm with minimum 240 cd/m<sup>2</sup> on white surface.
- 6 Simple parts clicking with each other ensuring fast installation.

#### Velos distance view


- Velos provides a solution regarding distance view and emergency exit signs
- Distance view from 30 up to 40 meters, minimizing the number of lights into an installation, reducing the energy consumption of the emergency lighting in a building and installation and maintenance cost.
- Various accessories for ease of installation aiming to accommodate all possible applications and areas, with recessed base, wall mounting accessories, lateral direction base, suspended from ceiling either with rope or metal pipes.



#### Velos optimal illumination

The exit sign plate used in Velos converts the high luminance of the LED into an illuminated surface with homogeneous brightness, with luminance of over 38 cd/m<sup>2</sup> on the white surface. As such the escape sign always remains easily recognisable even with poor visibility conditions or in bright surroundings.

Velos LEDs illuminate with a high efficiency of more than 112lm/W.



#### Photometric requirements for escape sign

EN 1838 (1999), Emergency lighting operation:

Lmin = 2 cd/m<sup>2</sup> (green surface) Lgreen  $\geq$  2 cd/m<sup>2</sup>

Lwhite  $\geq$  10 cd/m<sup>2</sup>

5 ≤ Lwhite / Lgreen ≤15

ISO 30061 (2007), When smoke is prime consideration:

Lgreen ≥ 10 cd/m<sup>2</sup> Lwhite ≥ 50 cd/m<sup>2</sup>



#### PSU unit of Velos (order separately)



Order code	Description	<del>(</del>	+-
O-ESC-3H	Velos PSU 3h	3h	4VTCs NiCd 1600mA
O-ESM-AT-3H	Velos PSU 3h Auto Test	3h	4VTCs NiMH 2000mA
O-ESC-3H-CGL	Velos PSU, 3h, CGL+	3h	4VTCs NiCd 1600mA
O-ESMAINS	Velos 230V Mains Slave		
O-ES-CG-S	Velos 220/230V Mains Slave CG-S		

#### Ceiling mount




PSU + Exit Sign → Velos

#### Wall mount







#### Recessed (30m)




# Ceiling mount (40m)









#### Recessed (40m)



## Suspended with metal pipes



#### Suspended with adjustable rope




# Lateral mount



# Accessories

Order code	Description			
O-ESA-RB	Velos Recessed base			
O-ESA-FLEX	Velos Wall FLEXI Joint			
O-ESA-RSA	Velos Wire suspension adjustable 150cm			
O-ESA-RSA-5M	Velos Wire suspension adjustable 5m			
O-ESA-PS30	Velos Pipe Suspension 48cm (ISO30061)			
O-ESA-LMB	Velos Lateral Mounting Base			
O-ESA-BMB	Velos Back Mounting Base			





# Exit sign of Velos

Order code [	Description	$\bigcirc$	Dimensions	
O-ESP-ILR	Velos pictogram ISO LEFT/RIGHT 30m	24 LEDs	288×165	<u>5</u> → ← 2
O-ESP-ID	Velos pictogram ISO DOWN/BLANK 30m	24 LEDs	288×165	<b>5</b> •
O-ESP-IDD	Velos pictogram ISO DOWN/DOWN 30m	24 LEDs	288×165	<b>5 4 4 2</b>
O-ESP-IU	Velos pictogram ISO UP/BLANK 30m	24 LEDs	288×165	<b>经</b>
O-ESP-IUU	Velos pictogram ISO UP/UP 30m	24 LEDs	288×165	<b>公</b> 个 汉
O-ESP-I2R	Velos pictogram ISO Lateral to Room	24 LEDs	288x165	<b>⅓ ⅔ ←</b>
O-ESP-I2W	Velos pictogram ISO Lateral to Wall	24 LEDs	288x165	<b>⅓ ⅓ ♦</b>
O-ESP-H	Velos Hydrant pictogram 30m	24 LEDs	288x165	HH
O-ESP-FHD	Velos Fire hose down 30m	24 LEDs	288×165	
O-ESP-FH-EXT	Velos Fire hose & extinguisher 30m	24 LEDs	288×165	
O-ESP-WIRL	Velos pictogram Wheel ISO LEFT/RIGHT 30m	24 LEDs	288×165	<b>&amp; → ←</b> &
O-ESP-WIDD	Velos pictogram Wheel ISO DOWN/DOWN 30m	24 LEDs	288x165	よりりる
Order code [	Description	8	Dimensions	
O-ESP40-ILR	Velos pictogram ISO LEFT/RIGHT 40m	24 LEDs	370×220	<b>☆ → ← </b>
O-ESP40-IDD	Velos pictogram ISO DOWN/DOWN 40m	24 LEDs	370x220	☆ ▼ ▼ №
O-ESP40-WILR	Velos pictogram Wheel ISO LEFT/RIGHT 40m	24 LEDs	370×220	<b>&amp; → ←</b> &
O-ESP40-WIDD	Velos pictogram Wheel ISO DOWN/DOWN 40m	24 LEDs	370×220	<b>&amp; ♥ ♥</b> &