



Specification

Voltage	10 - 30Vdc (*1)
Current	3m - 5mA (user selectable)
Light Output	>0.5Cd or 1Cd (user selectable)
Flash Rate	0.5Hz / 1Hz (user selectable)
Monitoring	Reverse polarity
Temperature	- 10°C to + 55°C
Protection	IP21C (s)* IP33C(d)*
Construction	ABS, PC lens
Weight	0.1Kg
Colour	Red
Flash colour	Red or amber

(*1) 110 / 230Vac when used with a Deep powered base.

(s)* Shallow Base

(d)* Deep / U Base

Solista

LED BEACON

LED beacons are available to complement audible alarms for use in areas where people may be present who have impaired hearing or areas with high ambient noise levels. LED technology offers a greatly reduced current consumption compared to Xenon types making them ideal for use with fire panels with restricted sounder circuit current capacity.

- ULTRA LOW CURRENT – LED TECHNOLOGY
- HIGH RELIABILITY
- LONG SERVICE LIFE
- LOCKING BASE
- COMPACT SIZE