



VERTICALLY ADJUSTABLE CABLE CHANNEL FITTING



- * VERTICALLY ADJUSTABLE SPLICES ARE DESIGNED TO BE USED FOR CONNECTING CABLE CHANNEL STRAIGHT SECTIONS WHEN A NON-STANDARD ANGLE IS NEEDED.
- * SPLICES ARE DESIGNED SO THAT A SEPARATE BONDING JUMPER IS NOT REQUIRED FOR ELECTRICAL CONTINUITY.
- * 3/8" MOUNTING HARDWARE IS INCLUDED AND SHOULD BE TORQUED TO 19 FT./LBS. TO ACHIEVE ELECTRICAL CONTINUITY.
- * UL APPROVED

PART NUMBER	CHANNEL WIDTH
9*-1643	3.00
9*-1644	4.00
9*-1646	6.00

- * - A = ALUMINUM
- ZN = ZINC ELECTROPLATED STEEL
- G = HOT DIP GALVANIZED STEEL AF
- SS4 = 304 STAINLESS STEEL
- SS6 = 316 STAINLESS STEEL



EATON, B-LINE DIVISION
509 WEST MONROE STREET
HIGHLAND, ILLINOIS 62249-0326
PHONE (618) 654-2184
FAX (618) 654-5499

TITLE: VERTICALLY ADJUSTABLE
CABLE CHANNEL FITTING

PRODUCT DWG. NO'S:

7913

SHEET OF

DRAWN BY:

DRAWING NO.
S00007913

DATE: 3/22/19

EQUIPMENT FURNISHED HAS BEEN FABRICATED
IN ACCORDANCE WITH THIS DRAWING.

THIS DRAWING AND/OR THE TECHNICAL INFORMATION CONTAINED HEREON IS THE PROPERTY OF EATON CORPORATION ("EATON"), AND IS ISSUED IN CONFIDENCE FOR EATON ENGINEERING PURPOSES ONLY AND MAY NOT BE REPRODUCED OR USED FOR ANY PURPOSE WHATSOEVER WITHOUT THE EXPRESS WRITTEN PERMISSION OF EATON TO THE USER. THIS DRAWING AND/OR TECHNICAL INFORMATION IS THE PROPERTY OF EATON AND IS LOANED FOR MUTUAL ASSISTANCE, TO BE RETURNED WHEN ITS INTENDED PURPOSE HAS BEEN SERVED.