



Certificate of Compliance

Certificate: 2414515

Master Contract: 240700

Project: 2652760

Date Issued: September 5, 2013

Issued to: Cooper Crouse-Hinds GmbH

Neuer Weg Nord 49

Eberbach, 69412

Germany

Attention: Jochen Guenther

The products listed below are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US or with adjacent indicator 'US' for US only or without either indicator for Canada only.



Johann Borabon

Issued by: Johann Borabon

PRODUCTS

CLASS 6233 06 - RECEPTACLES - Pin-and-Sleeve Type Plugs and Receptacles

CLASS 6233 86 - RECEPTACLES - Pin-and-Sleeve Type - Plugs and Receptacles - Certified to U.S. Standards

Cord Connector Cat. No.	Attachment Plug Cat. No.	Type	Rating
GH320C4W	GH320P4W	2P, 3 W	20 A, 125 V ac
GH320C6W	GH320P6W	2P, 3 W	20 A, 250 V ac
GH320C7W	GH320P7W	2P, 3 W	20 A, 480 V ac, 5 hp
GH420C12W	GH420P12W	3P, 4 W	20 A, 125/250 V ac
GH420C9W	GH420P9W	3P, 4 W	20 A, 3PH, 250 V ac
GH420C7W	GH420P7W	3P, 4 W	20 A, 3PH, 480 V ac, 5 hp
GH420C5W	GH420P5W	3P, 4W	20 A, 3PH, 600 V ac, 5 hp
GH520C9W	GH520P9W	4P, 5 W	20 A, 3PH-Y, 120/208 V ac
GH520C7W	GH520P7W	4P, 5 W	20 A, 3PH-Y, 277/480 V ac, 5 hp
GH520C5W	GH520P5W	4P, 5 W	20 A, 3PH-Y, 347/600 V ac, 5 hp
GH330C4W	GH330P4W	2P, 3 W	30 A, 125 V ac
GH330C6W	GH330P6W	2P, 3 W	30 A, 250 V ac
GH330C7W	GH330P7W	2P, 3 W	30 A, 480 V ac, 5 hp
GH430C12W	GH430P12W	3P, 4 W	30 A, 125/250 V ac
GH430C9W	GH430P9W	3P, 4 W	30 A, 3PH, 250 V ac



Certificate: 2414515

Master Contract: 240700

Project: 2652760

Date Issued: September 5, 2013

GH430C7W	GH430P7W	3P, 4 W	30 A, 3PH, 480 V ac, 5 hp
GH430C5W	GH430P5W	3P, 4W	30 A, 3PH, 600 V ac, 5 hp
GH530C9W	GH530P9W	4P, 5 W	30 A, 3PH-Y, 120/208 V ac
GH530C7W	GH530P7W	4P, 5 W	30 A, 3PH-Y, 277/480 V ac, 5 hp
GH530C5W	GH530P5W	4P, 5 W	30 A, 3PH-Y, 347/600 V ac, 5 hp
GH360C4W	GH360P4W	2P, 3W	60A, 125Vac
GH360C6W	GH360P6W	2P, 3W	60A, 250Vac
GH360C7W	GH360P7W	2P, 3W	60A, 480Vac
GH460C12W	GH460P12W	3P, 4W	60A, 125/250Vac
GH460C9W	GH460P9W	3P, 4W	60A, 3PH,250V ac
GH460C7W	GH460P7W	3P, 4W	60A, 3PH, 480Vac
GH460C5W	GH460P5W	3P, 4W	60A, 3PH, 600Vac
GH560C9W	GH560P9W	4P, 5W	60A, 3PH-Y, 120/208V
GH560C7W	GH560P7W	4P, 5W	60A, 3PH-Y, 277/480V
GH560C5W	GH560P5W	4P, 5W	60A, 3PH-Y, 347/600V
GH3100C4W	GH3100P4W	2P, 3 W	100 A, 125 V ac
GH3100C6W	GH3100P6W	2P, 3 W	100 A, 250 V ac
GH3100C7W	GH3100P7W	2P, 3 W	100 A, 480 V ac
GH4100C12W	GH4100P12W	3P, 4 W	100 A, 125/250 V ac
GH4100CB9W	GH4100P9W	3P, 4 W	100 A, 3PH, 250 V ac
GH4100C7W	GH4100P7W	3P, 4 W	100 A, 3PH, 480 V ac
GH4100C5W	GH4100P5W	3P, 4 W	100 A, 3PH, 600 V ac
GH5100C9W	GH5100P9W	4P, 5 W	100 A, 3PH-Y, 120/208 V ac
GH5100C7W	GH5100P7W	4P, 5 W	100 A, 3PH-Y, 277/480 V ac
GH5100C5W	GH5100P5W	4P, 5 W	100 A, 3PH-Y, 347/600 V ac
Receptacle	Power Inlet	Type	Rating
Cat. No.	Cat. No.		
GH320R4W	GH320B4W	2P, 3 W	20 A, 125 V ac
GH320R6W	GH320B6W	2P, 3 W	20 A, 250 V ac
GH320R7W	GH320B7W	2P, 3 W	20 A, 480 V ac, 3 hp
GH420R12W	GH420B12W	3P, 4 W	20 A, 125/250 V ac
GH420R9W	GH420B9W	3P, 4 W	20 A, 3PH, 250 V ac
GH420R7W	GH420B7W	3P, 4 W	20 A, 3PH, 480 V ac, 5 hp
GH420R5W	GH420B5W	3P, 4W	20 A, 3PH, 600 V ac, 5 hp
GH520R9W		4P, 5 W	20 A, 3PH-Y, 120/208 V ac



Certificate: 2414515

Master Contract: 240700

Project: 2652760

Date Issued: September 5, 2013

		4P, 5 W	20 A, 3PH-Y, 277/480 V ac, 5 hp
		4P, 5 W	20 A, 3PH-Y, 347/600 V ac, 5 hp
		2P, 3 W	30 A, 125 V ac
		2P, 3 W	30 A, 250 V ac
		2P, 3 W	30 A, 480 V ac, 5 hp
		3P, 4 W	30 A, 125/250 V ac
		3P, 4 W	30 A, 3PH, 250 V ac
		3P, 4 W	30 A, 3PH, 480 V ac, 5 hp
		3P, 4W	30 A, 3PH, 600 V ac, 5 hp
		4P, 5 W	30 A, 3PH-Y, 120/208 V ac
		4P, 5 W	30 A, 3PH-Y, 277/480 V ac, 5 hp
		4P, 5 W	30 A, 3PH-Y, 347/600 V ac, 5 hp
		2P, 3 W	60 A, 125 V ac
		2P, 3 W	60 A, 250 V ac
		2P, 3 W	60 A, 480 V ac
		3P, 4 W	60 A, 125/250 V ac
		3P, 4 W	60 A, 3PH, 250 V ac
		3P, 4 W	60 A, 3PH, 480 V ac
		3P, 4 W	60 A, 3PH, 600 V ac
		4P, 5 W	60 A, 3PH-Y, 120/208 V ac
		4P, 5 W	60 A, 3PH-Y, 277/480 V ac
		4P, 5 W	60 A, 3PH-Y, 347/600 V ac
		2P, 3 W	100 A, 125 V ac
		2P, 3 W	100 A, 250 V ac
		2P, 3 W	100 A, 480 V ac
		3P, 4 W	100 A, 125/250 V ac
		3P, 4 W	100 A, 3PH, 250 V ac
		3P, 4 W	100 A, 3PH, 480 V ac
		3P, 4 W	100 A, 3PH, 600 V ac
		4P, 5 W	100 A, 3PH-Y, 120/208 V ac
		4P, 5 W	100 A, 3PH-Y, 277/480 V ac
		4P, 5 W	100 A, 3PH-Y, 347/600 V ac

Notes:



Certificate: 2414515

Master Contract: 240700

Project: 2652760

Date Issued: September 5, 2013

Crouse-Hinds certified aluminum back boxes and angle adapters described under report 2636932 may be assembled with receptacles and power inlets listed above, except for inlet, Cat Nos GH560B9W, GH560B7W and GH560B5W.

APPLICABLE REQUIREMENTS

- CAN/CSA-C22.2 No 182.1-2007 - Plugs, Receptacles and Cable connectors of the pin and sleeve type
- UL 1682 (3rd Ed.) - Plugs, Receptacles and Cable connectors of the pin and sleeve type