

Eaton's Arrow Hart
Temporary power solutions

Mission critical
power when
and where you
need it

Arrow Hart



EATON

Powering Business Worldwide



Arrow Hart & Cam-Lok™ products are built tough to deliver safe, reliable temporary power for the most demanding industrial and commercial applications.

Table of contents	Page
Temporary power solutions	
Temporary power challenges and solutions	3
RhinoBox features & benefits	4
RhinoBox temporary power centers	5
RhinoBox accessories	6
Portable GFCI features and benefits	7
15A Portable GFCI	8
20A Portable GFCI	9
30A Portable GFCI	10
Watertight portable GFCI	11
Portable outlet box features & benefits	12
Portable outlet boxes, coverplates & accessories	13
Cam-Lok™ solutions	
J-Series applications, features & benefits	14
Posi-Lok™ applications, features & benefits	15

Entertainment

- Concerts
- Sporting events
- Film making
- Carnivals
- Trade shows

Industrial & commercial

- Maintenance
- Demolition
- New construction
- Plant additions

Stand-by power & emergency

- Disaster relief
- Gas stations
- Water treatment
- Cell towers

Temporary power you can depend on

The work force has trusted the Arrow Hart and Cam-Lok solutions to deliver power when safety is essential and timely job completion is mandatory. Eaton's Temp Power product offerings will keep you productive during the most extreme conditions.



Challenges

Limited receptacles

Multiple workers on a construction job site and everyone's running a power tool



Arrow Hart solutions

RhinoBox series

RhinoBox utilizes up to seven 20A weather resistant duplex receptacles to allow workers to plug in power tools, equipment, radios and lights



Challenges

Wet environment protection

Need to protect equipment and workers from ground faults however there is no GFCI around and the environment is wet or rainy



Arrow Hart solutions

Watertight GFCI

Portable GFCI with watertight plug and connectors provides NEMA 4X protection from harsh environments while offering automatic or manual GFCI protection



Challenges

Multiple rooms on-site

Need to string power to various rooms on a construction job site



Arrow Hart solutions

Multiple rooms on-site

RhinoBox and portable outlet boxes can be utilized together to spread power from one central location to each space



Challenges

Time-intensive assembly and disassembly

Temporary power requirements to an entertainment venue that needs to be set up and disassembled quickly and repeatedly



Cam-Lok™ solutions

J-series connector

Cam-Lok™ J-series connectors provide the ability to quickly connect and disconnect power without the use of tools



Challenges

Power needed fast

Temporary power for disaster relief after the storm



Cam-Lok™ solutions

Posi-Lok™ series connectors

The interlocked Posi-Lok™ power distribution system requires the user to connect and disconnect in sequence therefore providing a safe connection solution

Temporary power solutions

Get the power you need on the job

RhinoBox heavy-duty and E-series temporary power centers are designed to deliver safe and reliable temporary power in industrial and commercial job site conditions

RhinoBox features & benefits

“Plug & power” temporary power centers provide reliable power for construction sites, renovations, demolition, sporting events, entertainment venues, filmmaking, carnivals and more. Plug into the power of RhinoBox for all your temporary power needs.



See page 6 for E-Series temporary power centers

Compliances, specifications and availability are subject to change without notice.

Temporary power solutions


RhinoBox temporary power centers with GFCI protection

Product description

50A input, 20A, 30A, 50A output, 120/240 V/AC (max.)

Features

- Safely centralize and distribute temporary power on the job site
- Unique patented “stackable” design allows multiple RhinoBox units to lock together for safe transport and storage
- NEMA Type 3R rainproof enclosures
- Dedicated GFCI for each 125V receptacle
- Weatherproof receptacle covers protect from damage and weather
- Flip-up circuit breaker cover prevent accidental tripping



RB302A

RhinoBox



Rating A	V/AC	Distribution devices	Receptacle ratings	Protection Breaker †	GFCI	Catalog no.*	
50	120/240 Max.	(6) WR duplex receptacles	20A, 125V	✓	✓	RB300A	•
		(1) Locking receptacle	30A, 250V	✓	—		
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		
50	120/240 Max.	(6) Single receptacles	20A, 125V	✓	✓	RB301A	•
		(1) Locking receptacle	30A, 250V	✓	—		
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		
50	120/240 Max.	(6) Locking receptacles	20A, 125V	✓	✓	RB302A	•
		(1) Locking receptacle	30A, 250V	✓	—		
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		
50	120/240 Max.	(7) WR duplex receptacles	20A, 125V	✓	✓	RB3001A	•
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		


RhinoBox temporary power centers with GFCI protection E-series

Product description

50A input, 20A, 30A, 50A output, 120/240 V/AC (max.)

Features


- Safely centralize and distribute temporary power on the job site
- Unique patented “stackable” design allows multiple RhinoBox units to lock together for safe transport and storage
- NEMA Type 3R enclosures designed with two devices per circuit
- GFCI for each pair of 125V receptacles
- Weatherproof receptacle covers protect from damage and weather
- Flip-up circuit breaker cover prevent accidental tripping



RB300AE

RhinoBox E-series

Rating A	V/AC	Distribution devices	Receptacle ratings	Protection Overload	GFCI	Catalog no.*	
50	120/240 Max.	(6) WR duplex receptacles	20A, 125V	✓	✓	RB300AE	•
		(1) Locking receptacle	30A, 250V	✓	—		
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		
50	120/240 Max.	(6) Locking receptacles	20A, 125V	✓	✓	RB302AE	•
		(1) Locking receptacle	30A, 250V	✓	—		
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		



Plug
Non-NEMA
50A 125/250V
CA Standard

Receptacle
Non-NEMA
50A 125/250V
CA Standard

Testing & code compliance: cETLus listed for outdoor use - NEMA Type 3R products. Complies with NEC® Articles 525 & 590 & OSHA Reg. 29CFR, Part 1926, Subpart K, 1926.404, GFCI requirements. Conforms to UL1640 and CSA C22.2, no. 14.

Material characteristics: Enclosure: Cold-rolled 18 gauge steel. Legs: Cold-rolled 10 gauge steel.

Specification information: Please visit www.eaton.com/wiringdevices

Compliances, specifications and availability are subject to change without notice.

Indicates USMCA compliant

Temporary power distribution

RhinoBox temporary power centers accessories

Product description

50A input, 20A, 30A, 50A output, 120/240 V/AC (max.)











Features

- Use to connect RhinoBox to power sources and to additional RhinoBoxes in series
- Pro grip's tough nylon device housing resists impact in harsh environments
- Insulated body on cord sets for extra measure of safety
- Powerful cord-gripping capability helps eliminate conductor cord grip slip and strain on terminals





PC50A

Pro grip cord sets & adapters

Rating A	V/AC	Cord length	Description	Plug (male)	Connector (female)	Catalog no.	
50	125/250 Max	50 ft.	California style devices, 6/4 flexible black UL extension cord	 CS6365EX	 CS6364EX	<input type="checkbox"/> PC50A	•
		100 ft.	California style devices, 6/4 flexible black UL extension cord	 CS6365EX	 CS6364EX	<input type="checkbox"/> PC50B	•
		4 ft.	Non-NEMA 6/4 flexible black blank/bare wire connector		 CS6364EX	<input type="checkbox"/> PA50-6	•
		4 ft.	NEMA 14-30P 30A straight blade to 50A locking non-NEMA adapter	 5732AN	 CS6364EX	<input type="checkbox"/> A304WCSF	•
		4 ft.	NEMA 14-50P 50A straight blade to 50A locking non-NEMA adapter	 5752AN	 CS6364EX	<input type="checkbox"/> A504WCSF	•

RhinoBox replacement devices

Description	Catalog no.	
20A GFCI module (automatic reset)	<input type="checkbox"/> 20STGFMODA	
50A 125/250V locking outlet	<input type="checkbox"/> CS6369	•
50A outlet flip cover (black)	<input type="checkbox"/> 7788BK	•
20A 125V locking receptacle	<input type="checkbox"/> AHCL520R	•
30A 250V locking receptacle	<input type="checkbox"/> AHCL630R	•
20A/30A locking receptacle flip cover (gray)	<input type="checkbox"/> WP2	•
20A single straight blade receptacle	<input type="checkbox"/> 1877BK	•
20A duplex straight blade receptacle, weather-resistant (black)	<input type="checkbox"/> WRBR20BK	
Duplex receptacle damp location cover	<input type="checkbox"/> S1962BK-P	•



Testing & code compliance: cETLus listed for outdoor use - NEMA Type 3R products. Complies with NEC® Articles 525 & 590 & OSHA Reg. 29CFR, Part 1926, Subpart K, 1926.404, GFCI requirements. Conforms to UL1640 and CSA C22.2, no. 14. **Material characteristics:** Enclosure: Cold-rolled 18 gauge steel. Legs: Cold-rolled 10 gauge steel.

Specification information: Please visit www.eaton.com/wiringdevices

Compliances, specifications and availability are subject to change without notice.

 Indicates USMCA compliant

Industrial grade portable GFCIs

Portable protection from electrical injury

Arrow Hart's portable GFCIs give you the assurance that comes from knowing you are protected from ground fault hazards while on the job site

Portable GFCI features & benefits


Portable GFCIs offer exceptional protection against electrical shock when connected to power generators, agricultural equipment, portable electric heaters, submersible pumps, industrial washers, outdoor signs and vending equipment.

Available in a variety of cord lengths, with terminated devices or flying leads for field terminations



Related products

A full line of locking plugs and connectors, watertight devices, plus straight blade plugs & connectors provide many configuration options.



Compliances, specifications and availability are subject to change without notice.

Industrial grade portable GFCIs

15A Portable GFCIs

Product description

2-pole, 3-wire grounding
15A, 120 V/AC

Features

- High-strength polycarbonate housing for durability
- Compact body design
- NEMA Type 3R rated for indoor/outdoor use
- Field wireable versions available for attachment to existing cords or equipment power supply
- Automatic and manual GFCI reset options available



GFP11M1P3



GFI11M133



GFI11MN3

15A plug series - single & tri-tap

Rating A	V/AC	NEMA	NEMA Type	Connector style	Cord length	Cord gauge	Catalog no.*
15	120	5-15	3R	Single-tap	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFP11M1P3
				Tri-tap	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFP11M1P9
				Single-tap	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFP11M4P3
				Tri-tap	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFP11M4P9
				Flying leads - field wireable	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFP11MNP

† Only cRUus Listed

*Automatic reset GFCIs also available. When ordering automatic portable GFCIs replace "M" in Catalog number with "A".
Example: GFP11A1P3 = Automatic; GFP11M1P3 = Manual.

15A inline series - single & tri-tap

Rating A	V/AC	NEMA	NEMA Type	Connector style	Cord length	Cord gauge	Catalog no.*
15	120	5-15	3R	Single-tap	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI11M133
				Tri-tap	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI11M139
				Single-tap	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI11M233
				Tri-tap	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI11M239
				Single-tap	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI11M433
				Tri-tap	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI11M439
				Single-tap	50' (15.24m)	12/3 AWG	<input type="checkbox"/> GFI11M633
				Tri-tap	50' (15.24m)	12/3 AWG	<input type="checkbox"/> GFI11M639

*Automatic reset GFCIs also available. When ordering automatic portable GFCIs replace "M" in Catalog number with "A".
Example: GFI11A133 = Automatic; GFI11M133 = Manual.

15A inline series - field wireable

Rating A	V/AC	NEMA	NEMA Type	Connector style	Cord length	Cord gauge	Catalog no.*
15	120	5-15	3R	Molded	1' (0.3m)	12/3 AWG	<input type="checkbox"/> GFI11MN3

*Automatic reset GFCIs also available. When ordering automatic portable GFCIs replace "M" in Catalog number with "A".
Example: GFI11AN3 = Automatic; GFI11MN3 = Manual.

Industrial grade portable GFCIs

Industrial grade 20A portable GFCIs

Product description

2-pole, 3-wire grounding
20A, 120V/AC; 20A, 240V/AC



GFI12M1NN



GFI12M133

20A portable GFCIs, inline series



Rating A	V/AC	NEMA	NEMA Type	Connector style	Cord length	Cord gauge	Catalog no.*
20	120	N/A	4X	Flying leads - field wireable	2' (0.61m)	12/3 AWG	GFI12M1NN
				Flying leads - field wireable	6' (1.83m)	12/3 AWG	GFI12M2NN
				Flying leads - field wireable	25' (7.62m)	12/3 AWG	GFI12M4NN
				Flying leads - field wireable	50' (15.24m)	12/3 AWG	GFI12M6NN
20	240	N/A	4X	Flying leads - field wireable	2' (0.61m)	12/3 AWG	GFI22M1NN
				Flying leads - field wireable	6' (1.83m)	12/3 AWG	GFI22M2NN
				Flying leads - field wireable	25' (7.62m)	12/3 AWG	GFI22M4NN
				Flying leads - field wireable	50' (15.24m)	12/3 AWG	GFI22M6NN

*Automatic reset GFCIs are also available. When ordering automatic portable GFCIs replace "M" in catalog number with "A". Example: GFI12A1NN = Automatic; GFI12M1NN = Manual

Inline series - molded plug & connector



Rating A	V/AC	NEMA	NEMA Type	Connector style	Cord length	Cord gauge	Catalog no.
20	120	5-20	4X	Molded straight blade	2' (0.61m)	12/3 AWG	GFI12M133
				Molded locking	2' (0.61m)	12/3 AWG	GFI12M144
20	240	L6-20	4X	Molded locking	2' (0.61m)	12/3 AWG	GFI22M144

*Automatic reset GFCIs are also available. When ordering automatic portable GFCIs replace "M" in catalog number with "A". Example: GFI12A133 = Automatic; GFI12M133 = Manual

Accessories for 20A portable GFCIs



Description	Catalog no.	
20A 125V/AC NEMA 5-20 watertight plug	14W33	•
20A 125V/AC NEMA 5-20 watertight connector	15W33	•
Standard depth portable outlet box with flip lids	WD3059-DDN	•
20A 125V/AC NEMA 5-20 duplex straight blade receptacle - black	BR20BK	•
20A 125V/AC NEMA L5-20 color coded single receptacle	AHCL520R	•
20A 125V/AC NEMA 5-20 duplex straight blade corrosion resistant receptacle - yellow	AH5362CRY	•

Material characteristics: Polycarbonate body. Temperature rating: -35°C to 66°C (-31°F to 151°F).

Compliances, specifications and availability are subject to change without notice.



Indicates USMCA compliant

Industrial grade portable GFCIs

30A Portable GFCIs

Product description

2-pole, 3-wire grounding
 30A, 120 V/AC; 30A, 208 V/AC
 30A, 240 V/AC; 30A, 277 V/AC

Features

- Housing is high-strength polycarbonate for durability
- Compact body design
- NEMA Type 4X[†] wet location rated for indoor/outdoor use
- Field wireable versions available for attachment to existing cords or equipment power supply
- Automatic and manual GFCI reset options available



GFI13M1NN



GFI13M144

30A portable GFCIs, inline series, single phase



Rating A	V/AC	NEMA	NEMA Type	Connector style	Cord length	Cord gauge	Catalog no.*
30	120	N/A	4X	Flying leads - field wireable	2' (0.61m)	10/3 AWG	GFI13M1NN
				Flying leads - field wireable	6' (1.83m)	10/3 AWG	GFI13M2NN
				Flying leads - field wireable	25' (7.62m)	10/3 AWG	GFI13M4NN
				Flying leads - field wireable	50' (15.24m)	10/3 AWG	GFI13M6NN
				Flying leads - field wireable	100' (30.48m)	10/3 AWG	GFI13M7NN
30	208	N/A	4X	Flying leads - field wireable	2' (0.61m)	10/3 AWG	GFI93M1NN
				Flying leads - field wireable	6' (1.83m)	10/3 AWG	GFI23M1NN
30	240	N/A	4X	Flying leads - field wireable	2' (0.61m)	10/3 AWG	GFI23M1NN
				Flying leads - field wireable	6' (1.83m)	10/3 AWG	GFI23M2NN
				Flying leads - field wireable	25' (7.62m)	10/3 AWG	GFI23M4NN
				Flying leads - field wireable	50' (15.24m)	10/3 AWG	GFI23M6NN
				Flying leads - field wireable	100' (30.48m)	10/3 AWG	GFI23M7NN
30	277	N/A	4X	Flying leads - field wireable	2' (0.61m)	10/3 AWG	GFID3M1NN

*Automatic reset GFCIs are also available. When ordering automatic portable GFCIs replace "M" in catalog number with "A"
 Example: GFI13A1NN = Automatic; GFI13M1NN = Manual

Inline series - molded locking plug & connector



Rating A	V/AC	NEMA	NEMA Type	Connector style	Cord length	Cord gauge	Catalog no.
30	120	L5-30	4X	Molded locking	2' (0.61m)	10/3 AWG	GFI13M144
30	240	L6-30	4X	Molded locking	2' (0.61m)	10/3 AWG	GFI23M144

*Automatic reset GFCIs are also available. When ordering automatic Portable GFCIs replace "M" in catalog number with "A"
 Example: GFI13A144 = Automatic; GFI13M144 = Manual

Accessories for 30A portable GFCIs



Description	Catalog no.
30A 125V/AC NEMA L5-30 locking plug	AHCL530P
30A 125V/AC NEMA L5-30 locking connector	AHCL530C
30A 125V/AC NEMA L5-30 corrosion resistant locking plug	CRL530P
30A 125V/AC NEMA L5-30 corrosion resistant locking connector	CRL530C

Material characteristics: Polycarbonate body. Temperature rating: -35°C to 66°C (-31°F to 151°F).

Compliances, specifications and availability are subject to change without notice.

Indicates USMCA compliant

Industrial grade portable GFCIs

Watertight portable GFCIs

Product description

2-pole, 3-wire grounding
 15A, 120V/AC; 20A, 120V/AC; 20A, 240V/AC
 30A, 120V/AC; 30A, 240V/AC

Features

- Housing is high-strength polycarbonate for durability
- Compact body design
- Field wireable versions available for attachment to existing cords or equipment power supply
- Automatic and manual GFCI reset options available



GFI12M155

15A, 20A and 30A inline series - watertight plug and connector

Rating A	V/AC	NEMA	NEMA Type	Cord gauge	Plug type	Cord length	Catalog no.*
15	120	5-15	4X	12/3 AWG	Straight blade	2' (0.61m)	<input type="checkbox"/> GFI11M155
					Straight blade	6' (1.83m)	<input type="checkbox"/> GFI11M255
					Straight blade	25' (7.62m)	<input type="checkbox"/> GFI11M455
					Straight blade	50' (15.24m)	<input type="checkbox"/> GFI11M655
20	120	5-20	4X	12/3 AWG	Straight blade	2' (0.61m)	<input type="checkbox"/> GFI12M155
					Straight blade	6' (1.83m)	<input type="checkbox"/> GFI12M255
					Straight blade	25' (7.62m)	<input type="checkbox"/> GFI12M455
20	120	L5-20	4X	12/3 AWG	Locking	2' (0.61m)	<input type="checkbox"/> GFI12M166
					Locking	6' (1.83m)	<input type="checkbox"/> GFI12M266
					Locking	25' (7.62m)	<input type="checkbox"/> GFI12M466
20	240	L6-20	4X	12/3 AWG	Locking	2' (0.61m)	<input type="checkbox"/> GFI22M166
					Locking	6' (1.83m)	<input type="checkbox"/> GFI22M266
					Locking	25' (7.62m)	<input type="checkbox"/> GFI22M466
30	120	L5-30	4X	12/3 AWG	Locking	2' (0.61m)	<input type="checkbox"/> GFI13M166
					Locking	6' (1.83m)	<input type="checkbox"/> GFI13M266
					Locking	25' (7.62m)	<input type="checkbox"/> GFI13M466
30	240	L6-30	4X	12/3 AWG	Locking	2' (0.61m)	<input type="checkbox"/> GFI23M166
					Locking	6' (1.83m)	<input type="checkbox"/> GFI23M266
					Locking	25' (7.62m)	<input type="checkbox"/> GFI23M466

*Automatic reset GFCIs also available. When ordering automatic portable GFCIs replace "M" in Catalog number with "A".
 Example: GFI11A155 = Automatic; GFI11M155 = Manual.

Material characteristics: Polycarbonate body. Temperature rating: -35°C to 66°C (-31°F to 151°F).
Compliances, specifications and availability are subject to change without notice.

Portable outlet boxes

Built to withstand, deliver and perform

Arrow Hart's portable outlet boxes offer a safe, durable and efficient temporary power solution

Portable outlet box features & benefits

Rough and tough industrial grade portable outlet boxes are the bridge you need on location to provide safe power to industrial plants, building maintenance, food & beverage facilities, construction sites, shipyards, entertainment venues, filmmaking sets and expositions.



Related products

A wide range of wiring devices are available in many amperages that complement the portable outlet box line – straight blade receptacles, locking receptacles, plugs and more. These devices are offered in watertight, weather protective, isolated ground and corrosion resistant styles.



Compliances, specifications and availability are subject to change without notice.

Portable outlet boxes

Portable outlet boxes, cover plates & kits accessories

Product description

Standard depth box, extra depth box, feed through box, portable outlet box cover plates

Features

- Innovative one-piece design incorporates integrated strain relief and cover plate mounting holes (standard depth only)
- Rugged Alcryn® and Valox® materials provide durability in industrial applications
- Variety of standard and flip lid cover plates available for customized installations
- Non-conductive Alcryn® material provides protection against electric shock
- Large internal volume for ease of wiring



WD3059



WD3099



Cover plates

Portable outlet boxes



Description	Color	Catalog no.	
Standard depth	Y	□ WD3059 [∞] Δ	•
Extra depth	Y	□ WD3099 [∞]	•
Extra depth feed through	Y	□ WD3090F [∞]	•

Portable outlet box cover plates

Description	Diameter opening	Color	Catalog no.	
Duplex receptacle	–	BK	□ WD3051BK	•
Single receptacle	1.56" (3.96mm)	BK	□ WD3052BK	•
Single receptacle	1.39" (3.53mm)	BK	□ WD3054BK	•
Decorator style	–	BK	□ WD3055BK	•
Decorator style with flip lid	–	BK	□ WD3056BK	•
Duplex receptacle with flip lid	–	BK	□ WD3060BK	•
Blank plate	–	BK	□ WD3061BK	•


[∞]Noted Cat. nos. are Yellow boxes, also available in All-Black. For ordering Black, include Cat. no. followed by the color code: BK
 Δ cULus Listed

All Eaton's Wiring Devices' portable outlet boxes have compression fittings. Alcryn® is a registered trademark of Lyondellbasell Advanced Polymers Inc., Valox® is a registered trademark of Sabic Global Technologies B.V.

Cover plates available




Popular configurations example



Color information:

BK (Black), Y (Yellow)



Material characteristics: Flammability: Meets UL94 requirements, V0 rated. Environmental: Corrosion resistant, weather resistant to impact, heat, weather, oils, chemical, shock & UV exposure. Temperature rating: -35°C to 80°C (-31°F to 176°F).

Compliances, specifications and availability are subject to change without notice.

Indicates USMCA compliant

Cam-Lok™ J-series applications, features & benefits

Discover how Cam-Lok™ J-series connectivity outperforms hardwiring

Cam-Lok™ J-series connectors quickly replace traditional hardwiring and offer more safety with integrated watertight insulators and a strain relief system. Plus, a wide range of sizes, colors and accessories are available for complete flexibility

Features & benefits

Non-metallic retaining screw provides safe, strong and reliable contact retention

Easy assembly with standard tools

Retaining screw snaps into place to prevent loss



E-Z align drive pin increases torque and longitudinal strength 300%

Accommodates a wide range of cable sizes: #2 – 4/0

Double set screw termination for added strength (crimp also available)



Non-vulcanized E1016 & EZ1016 plugs feature a high-strength, molded-in-place locking ring to capture and secure the insulator to the contact

Fully insulated for direct mounting to steel panels

Threaded stud and double set screw receptacles available (other terminations available)

High impact-resistant thermoplastic protects receptacles from damage



Snapback covers provide NEMA 3R environmental seal



Wide range of colors available

See full product offering at Eaton.com

Posi-Lok™ applications, features & benefits

Quick and safe power distribution connection system

Designed to meet Article 520-53 Section K and Article 530-22 Section A (NEC) Standards, the built-in safety features require the user to connect or disconnect each plug in sequence. Protective receptacle covers cannot be raised until the preceding plug is locked into position.

Applications

- Posi-Lok™ power distribution panels bring a new level of safety to electrical power applications
- Posi-Lok™ systems utilize single conductor cable that can be used to full amperage capability without the need to derate like multi-conductor solutions
- Posi-Lok™ products are ideal for disaster relief, temporary power, standby emergency power and power distribution applications

Specifications

Electrical ratings

- 600 Volts
- 200 Amps continuous (E0200)
- 400 Amps continuous (E0400)

Temperature ratings

- -40° C to 105° C

Materials

- Cable sizes: #2-4/0
- Insulator: Elastomeric
- Contact: Copper

Environmental

- NEMA 3

Certifications

- UL Listed: E67181
- CSA certified: LR13963-48

Posi-Lok™ features & benefits

Safe, sequential interlock ensures ground mates first and breaks last

Limit switch capabilities



Reliable Posi-Lok™, cross-phase protection system ensures phase integrity


Quick and easy installation - Panels can be mounted into a standard 19-inch rack

UL Listed and CSA certified



Lockout-tagout compatible for safety and security

Shatter-resistant insulators and polarizing shells provide long-lasting, durable connectors



Double set screw termination for added strength and quick installation (crimp also available)

Plugs are uniquely keyed and color-coded to eliminate cross-phasing

See full product offering at Eaton.com

We make what matters work.*

* At Eaton, we believe that power is a fundamental part of just about everything people do. Technology, transportation, energy and infrastructure-these are things the world relies on every day. That's why Eaton is dedicated to helping our customers find new ways to manage electrical, hydraulic and mechanical power more efficiently, safely and sustainably. To improve people's lives, the communities where we live and work, and the planet our future generations depend upon. Because that's what really matters. And we're here to make sure it works.

See more at [Eaton.com/whatmatters](https://www.eaton.com/whatmatters)

Visit our website:
www.eaton.com/wiringdevices

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2022 Eaton
All Rights Reserved
Printed in USA
Publication No. BR620024EN
May 2022

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlan Km 17.8 s/n
Col. Villa Jardin esq.
Cerrada 8 de Mayo
Cuautitlan, Mexico CP 54800
Mexico
Eaton.mx
Eaton.com/wiringdevices

Follow us on social media to get the
latest product and support information.

