

LOFSORB™ activated carbon filter cartridges

Eaton's LOFSORB filter cartridges are suitable for the filtration of potable water, spirits, water based and organic solvents (for removal of colour, smell and taste contamination), galvanic bath (removal of organic contamination from nickel and copper baths).

LOFSORB activated carbon filter cartridges are characterized by a very good adsorption capacity, removing unwanted free chlorine and organic compounds from water or other liquids.

Features and benefits

- Economical alternative to granular carbon cartridges
- Pressed and extruded underhigh pressure
- Prevent carbon particles passing into the filtrate
- Excellent adsorption characteristics for chlorine and organic compounds

Design

Filter material

Bonded porous activated carbon block (85-90% coconut shell, 10-15% others)

Binder HDPE

Outside pre-filter

Type 01 and 04: Polypropylene fleece and net Type 02: Washed polypropylene yarn

Gaskets

Type 01 and 04: Ethylene-octene copolymer; Type 02: Polypropylene

Retention ratings (pre-filter)

Type 01 and 04: 1, 5, 10 µm Type 02: 5 µm

Technical data

Nominal lengths

Type 01: 4.875", 5", 9.75", 20", 30" (124, 127, 248, 508, 762 mm) Type 04: 9.75", 20" (248, 508 mm) Type 02: 5", 9.75", 10", 20", 30" (127, 248, 254, 508, 762 mm)

Outside diameters

Type 01: 2.8" (71 mm)¹ Type 04: 4.3" (110 mm) Type 02: 2.6" (65 mm)

Inside diameters

Type 01: 1.0" (26 mm) Type 04: 1.1" (28 mm) Type 02: 1.1" (27 mm)

Type 01: 4.875": 180 g

Recommended flow rate

2.11 gpm (8 l/min) per 10" element

Weights of active carbon

180 g 9.75": 360 g 20". 720 g 1,080 q Type 04: 9.75": 1,100 g 20": 2,200 g Type 02: 5": 9.75": 190 g 20": 380 g 570 g

Max. operating temperature

126 °F (52 °C)

Max. differential pressures


Type 01 and 04: 101 psid (7 bar) Type 02: 36 psid (2.5 bar)



LOFSORB activated carbon filter cartridges


Flow rate*

(70°F/21°C per 10" filter cartridge for water)



^{*} For liquids other than water, multiply pressure drop by fluid viscosity in centipoise.

Ordering code





North America

44 Apple Street Tinton Falls, NJ 07724 Toll Free: 800 656-3344 (North America only) Tel: +1 732 212-4700

Furone/Africa/Middle East Auf der Heide 2

53947 Nettersheim, Germany Tel: +49 2486 809-0

Friedensstraße 41 68804 Altlußheim, Germany Tel: +49 6205 2094-0

An den Nahewiesen 24 55450 Langenlonsheim, Germany Tel: +49 6704 204-0

No. 3, Lane 280, Linhong Road Changning District, 200335 Shanghai, P.R. China Tel: +86 21 5200-0099

100G Pasir Panjang Road #07-08 Singapore 118523 Tel: +65 6825-1668

Bua Clark 2061 - Macuco 13279-400 - Valinhos, Brazil Tel: +55 11 3616-8400

For more information, please email us at filtration@eaton.com or visit www.eaton.com/filtration

© 2018 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommenda-tions appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

FF-I A 05-2018





¹ Please note: Due to the outside diameter of 2.8" (71 mm), LOFSORB range 01 will not fit into the standard housing of the TOPCART™ range (from TKF-609 up). Special constructions are available upon request.

²Regarding the length selection and filter units for the various types, please refer to the relevant information on the first page.